



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2006SB Copper Splice Cap Crimp Conn, 18-10 Awg, 1, 000/Bag

Ideal

Catalog Number	2006SB
Manufacturer	Ideal
Description	Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 Awg, 18/2 Awg Min, 12/4 Awg Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V
Weight per unit	2.1 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Copper Sleeves
Voltage Rating	600

Material, Color, and Finish

Finish	Zinc-Plated, Tin-Plated Steel Sleeves
--------	---------------------------------------

Descriptions

Description	COPPER SPLICE CAP CRIMP CONN, 18-10 AWG, 1,000/BAG
extra long description	IDEAL 2006SB SPLICE CAP 10,000 BX
Features	Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D
Long Description	Buchanan, Crimp Connector, Splice Cap, Conductor Range: 18 - 10 AWG, 18/2 AWG Min, 12/4 AWG Max, Finish: Zinc-Plated, Tin-Plated Steel Sleeves, Material: Copper Sleeves, Voltage Rating: 600 V
Product Type	Splice Cap 10, 000 BX
Special Features	Features: For #18 To #10 AWG Wire; Minimum 2 #18 AWG; Maximum 4 #12 AWG; Use Buchanan C24 Crimp Tool; Designed For Fast, Permanent, Pressure-Type Connections; UL Listed And CSA Certified; Zinc-Plated Or Copper Sleeves Resist Corrosion; Solid Copper Sleeves Require Less Crimping Pressure; Resist Corrosion In Harsh Environments; UL 486C Listed And CSA C22.2 #188 Certified; Comply With Federal Specification W-S-61D

Manufacturer Information

Brand	Buchanan
GTIN	00781789452913
Manufacturers Part Number	2006SB
UPC	781789452913



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Splice Cap

Packaging

Carton	10000
Weight Per each	2.1

Uses, Certifications, and Standards

Application	For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections
standard	CSA, UL Listed, RoHS