ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



56331 STEEL FISH TAPE, 1/8" X 50'

KLEIN TOOLS

Catalog Number	56331
Manufacturer	KLEIN TOOLS
Description	The Klein Tools' 50-Foot Steel Fish Tape is perfect for wire runs associated with light commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. The large handle allows for a firm, steady grip as you pull the tape from the housing. The tape features laser-etched descending markings placed at every foot. These markings allow you to accurately measure the depth of conduit runs and determine the amount of tape left to pay
Weight per unit	1.5 (lbs/each)
Product Category	

Features

Material	Steel
Overall Height	8.81" (22.4 cm)
Overall Width	7.55" (19.2 cm)
Tape Size	50.0' x 1/8" x 0.045" (15.2 m x 0.3 cm x 0.1 cm)
Tensile Strength	—
Media	Yes
Package Quantity	1
Tape End	Double Loop Steel

Material, Color, and Finish

Color	Orange/Black

Dimensions and Weight

Diameter	7" (17.8 cm)
Overall Length	1.20" (3.0 cm)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	STEEL FISH TAPE, 1/8" X 50'
Features	The Klein Tools' 50-Foot Steel Fish Tape is perfect for wire runs associated with light commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. The large handle allows for a firm, steady grip as you pull the tape from the housing. The tape features laser-etched descending markings placed at every foot. These markings allow you to accurately measure the depth of conduit runs and determine the amount of tape left to pay
Long Description	The Klein Tools' 50-Foot Steel Fish Tape is perfect for wire runs associated with light commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. The large handle allows for a firm, steady grip as you pull the tape from the housing. The tape features laser-etched descending markings placed at every foot. These markings allow you to accurately measure the depth of conduit runs and determine the amount of tape left to pay
Product Type	50' Steel Fish Tape
Special Features	Optimized Housing Design
Extra Long Description	KLE 56331 50' Steel Fish Tape

Manufacturer Information

Brand	Klein Tools
GTIN	00092644563317
Manufacturers Part Number	56331
UPC	783523

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Steel Fish Tape

Packaging

Carton	1
Package	5
Weight	1.5 lb (680.4g)
Weight Per Each	1.5 (lbs/each)

Uses, Certifications, and Standards

Application	Wire Pulling
Standard	—


FISH TAPES
KLEIN
EST. 1857
TOOLS
REDESIGNED
FOR THE ELECTRICIAN
KLEIN TOOLS
STEEL FISH TAPE
GUÍA JALACABLES DE ACERO
RUBAN DE TIRAGE EN ACIER
240'
LASER MARKINGS
MADE IN USA
240'
(73.1 m)


THE FISH TAPE DESIGNED WITH YOU IN MIND

The Klein Tools' Fish Tapes are perfect for commercial, residential and voice-data-video wire installations. The optimized angle of the tape reduces payout effort while also limiting binding. A multiple position handle design and the unique interior case makes rewinding tape far easier. Our updated fish tapes feature laser etched descending marks to measure conduit and remaining tape.




SQUARE IS FOR LEVERAGE.
CIRCULAR IS FOR COMFORT.
OUR UNIQUE HYBRID SHAPE PROVIDES LEVERAGE AND COMFORT.







MULTI-POSITION HANDLE GIVES YOU A FIRM, STEADY GRIP AS YOU PAY OUT AND REWIND TAPE.



OPTIMIZED FOR SMOOTHER PAY OUT AND EASIER REWIND.

ALL FISH TAPES

- Laser etched markings in 1-foot (0.3 m) increments allow you to accurately measure the depth of conduit runs and determine the amount of tape left to pay out (not available on Multi-Groove fish tapes)
- Designed to decrease payout effort by optimizing the tape payout angle
- Polypropylene case and handle offer excellent impact resistance



FIBERGLASS

(56350, 56351, 56380, 56382, 56383)



- **The Multi-Groove Fish Tapes** (56380, 56382, 56383) have multiple grooves molded into the fiberglass tape providing smoother tape feeding, excellent flexibility, and rigidity when you need it
- Our strong S-Glass fiberglass has better pushing power and a longer life while maintaining its low-friction exterior and great maneuverability
- Redesigned, non-conductive, nylon tip on the 56382 and 56383 is now stronger, smoother, and narrower to maneuver in crowded conduit. Flexible spiral steel leaders are available on 56350, 56351, 56380



STEEL

(56331, 56333, 56334, 56340, 56341)

- Improved **High-Carbon Steel Fish Tapes** (56333, 56334) are firm yet flexible for long runs and large wire pulls
- New protective coating reduces non-contact moisture and humidity but keeps the steel dry to touch
- **Stainless Steel Fish Tapes** (56340, 56341) won't corrode in humid or damp conditions
- Double-Loop creates a stronger, snag resistant end for maneuvering through conduit



KLEIN HAS THE RIGHT FISH TAPE FOR YOUR INDUSTRIAL, COMMERCIAL, RESIDENTIAL AND VDV WIRE INSTALLATIONS.



Cat. No	UPC 0-92644+	Tape Material	Tape Length	End/Leader	Overall Dimensions	Weight
56331	56331-7	Steel	50-ft (15 m)	Double-Loop	1.2" x 7.6" x 8.8" (3.0 x 19.2 x 22.4 cm)	1.5 lb (680.4g)
56333	56333-1	Steel	120-ft (37 m)	Double-Loop	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	5.0 lb (2.3 kg)
56334	56334-8	Steel	240-ft (73 m)	Double-Loop	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	7.9 lb (3.6 kg)
56340	56340-9	Stainless Steel	125-ft (38 m)	Double-Loop	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	5.1 lb (2.3 kg)
56341	56341-6	Stainless Steel	240-ft (73 m)	Double-Loop	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	7.9 lb (3.6 kg)
56350	56350-8	Fiberglass	50-ft (15 m)	Spiral Steel Leader	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	2.8 lb (1.3 kg)
56351	56351-5	Fiberglass	100-ft (30 m)	Spiral Steel Leader	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	3.4 lb (1.5 kg)
56380	56380-5	Multi-Groove Fiberglass	100-ft (30 m)	Spiral Steel Leader	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	3.4 lb (1.5 kg)
56382	56382-9	Multi-Groove Fiberglass	50-ft (15 m)	Nylon Eyelet	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	2.7 lb (1.2 kg)
56383	56383-6	Multi-Groove Fiberglass	100-ft (30 m)	Nylon Eyelet	1.9" x 12.4" x 16.2" (4.7 x 31.4 x 41.2 cm)	3.3 lb (1.5 kg)

Cat. Nos. 56331, 56333, 56334, 56340, 56341 -- U.S. Pat.: 8164025; 8168921; 8212178; 9895773; 10099316

PROUDLY MADE IN USA
with Global Components

KLEIN TOOLS®

See our complete line of **Wire Pulling Tools**
www.kleintools.com

© 2019 Klein Tools, Inc.
Lincolnshire, IL 60069
82876 Rev. 10/19 A