ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10917 Mill Creek Rd
Lenexa, KS 66219-0000
Phone: 9135637000
Fax: 9135637050



65656 40W 3/4/5K CCT SELECTABLE SMALL WALL PACK

SATCO

Catalog Number	65656
Manufacturer	SATCO
Description	40 Watt Small LED Wall Pack with Integrated Bypassable Photocell - CCT Selectable - 120-277 Volts - Dusk to Dawn Security Lighting - IP65 - Bronze Finish
Weight per unit	5.3 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	ADC12 and PC
Number Of Lamps	1
Socket Type	Integrated
Voltage Rating	120 to 277 v
Warranty	5 Year Limited - Fixtures
Surge Protection	Built-in surge protection - 2.5KV

Material, Color, and Finish

Style	Traditional
Fixture Material	Aluminum / Polycarbonate (PC)

Dimensions and Weight

Size	W:8.50 H:8.44 E:7.45

Descriptions

Description	40W 3/4/5K CCT SELECTABLE SMALL WALL PACK
Long Description	40 Watt Small LED Wall Pack with Integrated Bypassable Photocell - CCT Selectable - 120-277 Volts - Dusk to Dawn Security Lighting - IP65 - Bronze Finish
Product Type	40W Led Small Wall Pack
Special Features	Beam Angle (degree): 80;CCT (Kelvin Temp): 3000K/4000K/5000K;Cct Selectable: True;FCC Compliant: True;Hours Rated: 50000;Indoor Outdoor: Outdoor;IP Rating: IP65;Lumens: 4200L-5000L;Operating Temp: -40C (-40F) to +45C (+113F);Photo Cell: Yes - Bypassable;Warranty: 5-Years;Watts: 40W
Extra Long Description	SATCO 65/656 40W LED SMALL WALL PAC

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10917 Mill Creek Rd
Lenexa, KS 66219-0000
Phone: 9135637000
Fax: 9135637050

Manufacturer Information

Brand	Satco
	Nuvo
GTIN	00045923651762
Manufacturers Part Number	65/656
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

Packaging

Carton	1
Weight	5.08
Weight Per Each	5.3 (lbs/each)

Uses, Certifications, and Standards

Application	Wall Pack
Operating Temperature	-40C (-40F) to a maximum of +50C (+122F)
Environmental Conditions	Wet
Standard	cULus - Certified