ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



65902 20W 2 HEAD SECURITY LIGHT W/CAMERA 1900LM - BROWN

SATCO

Catalog Number	65902
Manufacturer	SATCO
Description	Bullet Outdoor SMART Security Camera - Starfish Enabled - Brown Finish
Weight per unit	2.8 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED

Material, Color, and Finish

Style	Industrial
Fixture Material	Die Cast Aluminum

Descriptions

Description	20W 2 HEAD SECURITY LIGHT W/CAMERA 1900LM - BROWN
Long Description	Bullet Outdoor SMART Security Camera - Starfish Enabled - Brown Finish
Product Type	Bullet Sec LGT W/ Camera - BR
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - Fixtures ; Brand: Starfish ; Watts: 20 ; Lumens: 1900 ; CCT: 3000K ; Color Temperature: Warm White ; CRI: 80 ; Dimmable: Only with Starfish App ; FCC Compliant: Yes ; Lamp Base: Integrated ; Hours Rated: 50000 ; Width: 8.27 in. ; Height: 8.46 in. ; Extends: 9.45 in. ; Weight: 2.78 lb. ; ADA Compliant: No ; California T24 Compliant ; Incandescent Equivalent: 100W ; Includes: Camera and speaker ; Indoor/Outdoor: Outdoor ; Installation Notes: Must be
Extra Long Description	SATCO 65/902 BULLET SEC LGT W/ CAME

Manufacturer Information

Brand	Satco Nuvo
GTIN	00045923659706
Manufacturers Part Number	65/902
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Security Light with Camera

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	1
Package	5
Weight Per Each	2.8 (lbs/each)

Uses, Certifications, and Standards

Application	Security Lighting
Environmental Conditions	Wet location
Standard	cETLus Listed

SATCO | NUVO

Project Name

Location | Prepared By



NUVO 65-902

BULLET SEC LGT W/ CAMERA - BR

Notes

[www] 08-22-2022 00:35:11

General

Status	Active
Finish	Brown
Wattage	20W
Style	Utility
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	8.27
Height (in.)	8.46
Extension (in.)	9.45
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	Yes
Operational Humidity	20% to 85% non-condensing
Communication Protocol	802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings
Software Supported	Cloud Storage
Storage Capacity	Micro SD Card to 128GB

Specifications

Technology	LED
CRI	80
Lumen Output	1900L
Rated Hours	50000
Voltage	120V-277V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable Only with Starfish App
Beam Angle	50
Operating Temperature	-20C (-4F) to +60C (+140F)
Weight (lb.)	2.78
Sloped Ceiling	No
Fixture Material	Metal
Fixture Type	Security Camera

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Compliant - Outdoor LED
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Compliant
California Prop 65	Lead
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Installation Notes	Must be wired to recessed junction boxes ONLY.
Warranty	5 Year Limited

Copyright 2020 Satco Products, Inc.
All Rights Reserved