# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## 8300I Hosp GRD Dup Recept 20A/125VAC I

*Pass & Seymour/Legrand*

| | |
|---|---|
| Catalog Number | 8300I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and, Side Wire 20AMP 125voltivory |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

## Features

| | |
|---|---|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| Material | Nylon;Other |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

## Material, Color, and Finish

| | |
|---|---|
| Color | Ivory |

## Dimensions and Weight

| | |
|---|---|
| Height | 3.281 |
| Size | 1.625 L x .900 W x 3.281 H |
| Width | .900 |

## Descriptions

| | |
|---|---|
| Description | HOSP GRD DUP RECEPT 20A/125VAC I |
| extra long description | P&S 8300I HOSP GRD DUP RECEPT 20A/1 |
| Long Description | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and, Side Wire 20amp 125voltIvory |
| Product Type | Hosp GRD Dup Recept 20A/125VAC I |
| Special Features | One-piece nickel-plated brass mounting strap with integral ground. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. Exclusive patented feature, circuit label on face allows permanent circuit identification. .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Manufacturer Information

| | |
|---|---|
| Brand | Pass and Seymour |
| GTIN | 00785007830095 |
| Manufacturers Part Number | 8300I |
| sub brand | Pass & Seymour |
| UPC | 785007830095 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Commercial receptacles |
| Type | Hospital Grade Receptacle, Extra Heavy-Duty |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.25 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 and UL94-5 VA |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | cULus UL498, CSA C22.2 No. 42 |
| Temperature Rating | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |