PASS & SEYMOUR®

radiant® Tamper-Resistant Receptacles 15A, 125V

Safety- and code-driven solutions brought to you by Legrand.

885TR, 885TRNA, 885TRS, 885TRWR

Aesthetically improved yet reliable as ever, these tamper-resistant receptacles are equipped with a patented shutter system—now with black "invisi-shutters" that disappear for an invisible effect preferred by end users—to help prevent improper insertion of foreign objects. These UL listed receptacles comply with 2014 NEC® Article 406.12, and as part of the radiant® collection, now offer a better fit, form and finish. Ideal for residential, multi-dwelling and hospitality applications.

Features & Benefits



Extra-long strap

High-impact resistant thermoplastic construction.

Protects children: patented shutter system — now with black "invisi-shutters" that disappear for an invisible effect — helps prevent improper insertion of foreign objects.

885TRLA

- **Part of the radiant® collection.**
- **Meets National Electrical Code® Tamper-Resistant requirements.**
- **Quickloop wire looping aid.**
- **Long-term blade retention.**
- **Longer tri-drive screws** for easier 12 AWG looping.
- **Extra-large circuit break-off tabs.**
- **Side-access push wire release.**
- **Ultrasonic welding** of face to back body.
- **Side wire** accepts #12 – #14 AWG solid wire.
- **Push wire** accepts #14 AWG solid only.
- **Superior protection** to traditional outlet "caps" or "protection plates."
- **Low profile face.**
- **Self-grounding models** provide automatic ground clip.

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498, CSA/CUL approved. cULus listed. Standard CSA C22.2 No. 42. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	2000V Min.
Maximum Working Voltage	125V
Current Interrupting	15A
Temperature Rise	30° Max.
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#12 - #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	Complies with UL498



885TRSLA

Materials	
Face	Thermoplastic (PVC)
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.040 Zinc-Plated Steel
Ground Contacts	Brass
Tamper-Resistant Shutters	Thermoplastic (Delrin)
Terminal Screws	#8 Tri-Drive Plated Steel
Ground Screw	#8, Hex Tri-Drive, Plated Steel, Green Chromate
Auto-Ground Clip	Plated Steel
Mounting Screws	#6, Tri-Drive, Steel

Warranty

1 Year

Ordering Information

Tamper-Resistant Receptacles

Catalog Number	Rating A	Rating VAC	Color	NEMA Config. No.	3rd Party Compliance UL498	C22.2 No. 42	cULus
885TRI	15	125	Ivory	5-15R	•	•	•
885TRW	15	125	White	5-15R	•	•	•
885TR	15	125	Brown	5-15R	•	•	•
885TRGRY	15	125	Gray	5-15R	•	•	•
885TRBK	15	125	Black	5-15R	•	•	•
885TRLA	15	125	Light Almond	5-15R	•	•	•
885TRNICC12	15	125	Nickel	5-15R	•	•	•
885TRDBCC12	15	125	Dark Bronze	5-15R	•	•	•
Self-Grounding Tamper-Resistant Receptacles							
885TRSI	15	125	Ivory	5-15R	•	•	•
885TRSW	15	125	White	5-15R	•	•	•
885TRSLA	15	125	Light Almond	5-15R	•	•	•
Tamper-Resistant, Weather-Resistant Receptacles							
885TRWR	15	125	Brown	5-15R	•	•	•
885TRWRI	15	125	Ivory	5-15R	•	•	•
885TRWRLA	15	125	Light Almond	5-15R	•	•	•
885TRWRW	15	125	White	5-15R	•	•	•
NAFTA-Compliant Tamper-Resistant Receptacles							
885TRNAI	15	125	Ivory	5-15R	•	•	•
885TRNAW	15	125	White	5-15R	•	•	•
885TR	15	125	Brown	5-15R	•	•	•
885TRNAGRY	15	125	Gray	5-15R	•	•	•
885TRBK	15	125	Black	5-15R	•	•	•
885TRNALA	15	125	Light Almond	5-15R	•	•	•

2 Pole, 3 Wire

NEMA 5-15R

Vertical Markets

- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Home Automation Controls**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Sensors**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Screwless Wall Plates**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20197 June 2016 **©2016 Legrand All Rights Reserved**

PASS & SEYMOUR®

radiant® Tamper-Resistant Receptacles 15A, 125V

Safety- and code-driven solutions brought to you by Legrand.

885TR, 885TRNA, 885TRS, 885TRWR

Aesthetically improved yet reliable as ever, these tamper-resistant receptacles are equipped with a patented shutter system—now with black "invisi-shutters" that disappear for an invisible effect preferred by end users—to help prevent improper insertion of foreign objects. These UL listed receptacles comply with 2014 NEC® Article 406.12, and as part of the radiant® collection, now offer a better fit, form and finish. Ideal for residential, multi-dwelling and hospitality applications.

Features & Benefits



Extra-long strap

High-impact resistant thermoplastic construction.

Protects children: patented shutter system — now with black "invisi-shutters" that disappear for an invisible effect — helps prevent improper insertion of foreign objects.

885TRLA

- **Part of the radiant® collection.**
- **Meets National Electrical Code® Tamper-Resistant requirements.**
- **Quickloop wire looping aid.**
- **Long-term blade retention.**
- **Longer tri-drive screws** for easier 12 AWG looping.
- **Extra-large circuit break-off tabs.**
- **Side-access push wire release.**
- **Ultrasonic welding** of face to back body.
- **Side wire** accepts #12 – #14 AWG solid wire.
- **Push wire** accepts #14 AWG solid only.
- **Superior protection** to traditional outlet "caps" or "protection plates."
- **Low profile face.**
- **Self-grounding models** provide automatic ground clip.

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498, CSA/CUL approved. cULus listed. Standard CSA C22.2 No. 42. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	2000V Min.
Maximum Working Voltage	125V
Current Interrupting	15A
Temperature Rise	30° Max.
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#12 - #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	Complies with UL498



885TRSLA

Materials	
Face	Thermoplastic (PVC)
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.040 Zinc-Plated Steel
Ground Contacts	Brass
Tamper-Resistant Shutters	Thermoplastic (Delrin)
Terminal Screws	#8 Tri-Drive Plated Steel
Ground Screw	#8, Hex Tri-Drive, Plated Steel, Green Chromate
Auto-Ground Clip	Plated Steel
Mounting Screws	#6, Tri-Drive, Steel

Warranty

1 Year

Ordering Information

Tamper-Resistant Receptacles

Catalog Number	Rating A	Rating VAC	Color	NEMA Config. No.	3rd Party Compliance UL498	C22.2 No. 42	cULus
885TRI	15	125	Ivory	5-15R	•	•	•
885TRW	15	125	White	5-15R	•	•	•
885TR	15	125	Brown	5-15R	•	•	•
885TRGRY	15	125	Gray	5-15R	•	•	•
885TRBK	15	125	Black	5-15R	•	•	•
885TRLA	15	125	Light Almond	5-15R	•	•	•
885TRNICC12	15	125	Nickel	5-15R	•	•	•
885TRDBCC12	15	125	Dark Bronze	5-15R	•	•	•
Self-Grounding Tamper-Resistant Receptacles							
885TRSI	15	125	Ivory	5-15R	•	•	•
885TRSW	15	125	White	5-15R	•	•	•
885TRSLA	15	125	Light Almond	5-15R	•	•	•
Tamper-Resistant, Weather-Resistant Receptacles							
885TRWR	15	125	Brown	5-15R	•	•	•
885TRWRI	15	125	Ivory	5-15R	•	•	•
885TRWRLA	15	125	Light Almond	5-15R	•	•	•
885TRWRW	15	125	White	5-15R	•	•	•
NAFTA-Compliant Tamper-Resistant Receptacles							
885TRNAI	15	125	Ivory	5-15R	•	•	•
885TRNAW	15	125	White	5-15R	•	•	•
885TR	15	125	Brown	5-15R	•	•	•
885TRNAGRY	15	125	Gray	5-15R	•	•	•
885TRBK	15	125	Black	5-15R	•	•	•
885TRNALA	15	125	Light Almond	5-15R	•	•	•

2 Pole, 3 Wire

NEMA 5-15R

Vertical Markets

- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Home Automation Controls**
- **Paddle Switches**
- **Lighting & Fan Controls**
- **Timers**
- **Sensors**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Screwless Wall Plates**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20197 June 2016 **©2016 Legrand All Rights Reserved**