



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



300GCX120 300GCX Selectone Hazloc Speaker

Federal Signal Corp.

Catalog Number	300GCX120
Manufacturer	Federal Signal Corp.
Description	Selectone 15 Watt Amplified Speaker, Hazardous Location, 120VAC, Gray - Available In 24VAC/DC, 120VAC and 240VAC. Reliable, Solid-State Circuitry. Digital Signal Amplification. Fused Input and Output. Built-In Gain Control, Adjustable Between 0 DbA to 110 DbA At 10 Feet (0 DbA to 120 DbA At 1 Meter). Cast Copper Free Aluminum Housing, Spun Aluminum Projector. Type 4X, IP66 Enclosure. IP69K Compliant. Indoor/Outdoor Use. CSFM Approved. UL and CUL Listed For Class I, Division 2, Groups A, B, C and D & Class
Weight per unit	6.5 (lbs/each)
Product Category	Sound & Audio Systems

Features

dimensions	12.4 H x 7.9 W x 8.5 D
Material	Die-Cast Aluminum
Operating Current	0.20
Operating Voltage	120VAC 50-60Hz
Output Level	15

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	300GCX SELECTONE HAZLOC SPEAKER
extra long description	FED-SIG 300GCX-120 15W AMPLIFIED SP
Long Description	SelecTone 15 Watt Amplified Speaker, Hazardous Location, 120VAC, Gray - Available in 24VAC/DC, 120VAC and 240VAC. Reliable, solid-state circuitry. Digital signal amplification. Fused input and output. Built-in gain control, adjustable between 0 dBa to 110 dBa at 10 feet (0 dBa to 120 dBa at 1 meter). Cast copper free aluminum housing, spun aluminum projector. Type 4X, IP66 enclosure. IP69K compliant. Indoor/outdoor use. CSFM Approved. UL and cUL Listed for Class I, Division 2, Groups A, B, C and D & Class
Product Type	15W Amplified Speaker 120V Haz Loc
Special Features	Digital Signal Amplification



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Federal Signal
GTIN	00782979200376
Manufacturers Part Number	300GCX-120
UPC	782979200376

Taxonomies, Classifications, and Categories

Type	Hazardous Location Amplified Speaker
------	--------------------------------------

Packaging

Carton	1
Weight Per each	6.5

Uses, Certifications, and Standards

Application	Indoor/Outdoor
Enclosure	Type 4X, IP66, IP69K
Mounting	SURFACE
Operating Temperature	-67 to 150
standard	UL Listed/cUL Listed/CSFM Approved