



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 267RT 3" Diecast Emt Raintight Compression Coupling

Bridgeport Fittings

|                  |                       |
|------------------|-----------------------|
| Catalog Number   | 267RT                 |
| Manufacturer     | Bridgeport Fittings   |
| Description      | 3" Raintight Coupling |
| Weight per unit  | 2.2 (lbs/each)        |
| Product Category | Liquid Tight Fittings |

### Features

|                  |                             |
|------------------|-----------------------------|
| Connector Type   | Compression                 |
| Material         | Zinc Die Cast               |
| media            | Yes                         |
| outside diameter | 103.6320;4.0800000000000000 |

### Dimensions and Weight

|        |                             |
|--------|-----------------------------|
| Length | 101.6000;4.0000000000000000 |
|--------|-----------------------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 3" DIECAST EMT RAINLIGHT COMPRESSION COUPLING   |
| extra long description | BPT 267-RT 3" RAINLIGHT CPLG  |
| Features               | Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.  |
| Long Description       | 3" Raintight Coupling   |
| Product Type           | 3" Raintight CPLG   |
| Special Features       | With Bridgeport's newly redesigned Raintight Compression Couplings, 266-RT through 269-RT, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. |

### Manufacturer Information

|                           |                     |
|---------------------------|---------------------|
| Brand                     | Bridgeport Fittings |
| GTIN                      | 00781747142672      |
| Manufacturers Part Number | 267RT               |
| UPC                       | 781747142672        |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | DIECAST EMT FITTINGS |
| Type                 | Raintight            |

### Trade Size

|            |   |
|------------|---|
| Trade Size | 3 |
|------------|---|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 12    |
| Weight Per each | 2.208 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

These 3" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAINIGHT" clearly cast into the body. This marking helps the AHJ to precisely confirm the products intended use. Patented

standard

cULus