ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

A200M4CAC A200 - Starter Size 4 Open 3 Pole 120V/60HZ Coil

Eaton Corp

Catalog Number	A200M4CAC
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Starter, 120V/60 HZ or 110V/50 HZ Coil Voltage, 135A, Three-Pole, Size 4, 40 HP At 208V, 50 HP At 240V, 100 HP At 480, 600V, A200 Series, Wired For Separate Control
Weight per unit	10.4 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

dimensions	6.7500 IN X 6.6300 IN X 4.6300 IN
Poles	Three-pole

Dimensions and Weight

Size	4

Descriptions

Description	A200 - STARTER SIZE 4 OPEN 3 POLE 120V/60HZ COIL
extra long description	ETN A200M4CAC Eaton A200 NEMA motor
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 120V/60 Hz or 110V/50 Hz coil voltage, 135A, Three-pole, Size 4, 40 hp at 208V, 50 hp at 240V, 100 hp at 480,600V, A200 series, Wired for Separate Control
Product Type	Eaton A200 Nema Motor Control
Special Features	Wired for separate control

Manufacturer Information

Brand	Eaton
GTIN	00786678007199
Manufacturers Part Number	A200M4CAC
UPC	786678007199

Taxonomies, Classifications, and Categories

Type	Motor Control

Packaging

Carton	1
Weight Per each	10.35

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed,CSA Certified