ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

ACP6044BC 60A 4W4P P&S Plug (600VAC/250VDC)

Appleton/Oz Gedney

Catalog Number	ACP6044BC
Manufacturer	Appleton/Oz Gedney
Description	Powertite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 4, Number Of Wires: 4, Wire Size: 6 - 2 Awg (Building), 6 - 4 Awg (Extra Flex), Amperage Rating: 60 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase: 3
Weight per unit	3.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	60
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	4
Phase	3
Poles	4
Voltage Rating	600//250
Wire Size	6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex)

Descriptions

Description	60A 4W4P P&S PLUG (600VAC/250VDC)
extra long description	APP ACP6044BC 60A CLAMP RING PLUG 4
Long Description	Powertite Grounding Style 1 Metallic Clamping Ring Plug, Number Of Poles: 4, Number Of Wires: 4, Wire Size: 6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex), Amperage Rating: 60 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase: 3
Product Type	60A Clamp Ring Plug 4W4P ST1
Special Features	Grounding style: Shell only; Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus; Ideal for use on shipping docks, ports and other ship to shore applications; Suitable for use in locations where a weatherproof enclosure is required; Rough usage construction; Natural finish glass filled polyester insulating blocks; Locking screw and slot prevents plug cable collar from backing off; Wire r

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Appleton
GTIN	00781381440233
Manufacturers Part Number	ACP6044BC
sub brand	Powertite
UPC	781381440233

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 1 Metallic Clamping Ring Plug

Packaging

Carton	6
Weight Per each	3.02

Uses, Certifications, and Standards

Application	For ADR6044 Receptacle And ARC6044BC Connector Body
environmental conditions	Temperature Rating: -40 To 107 DEG C
nema rating	NEMA 3, 3R, 4, 4X
standard	UL 1682, UL 1686, UL 50E; UL Listed: E145916, E145917; CSA Standard: C22.2 No. 182.1; CSA Certified: 065179; NEMA FB11