



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3024124XS Encl 30X24X12 N4X SS CH Clamp CVR

*Cooper B-Line/Cable Tray*

Catalog Number	3024124XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 30" Height, 12" Length, 24" Width, Nema 4X, Hinged Cover, 4XS Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	66.3 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

dimensions	12.0000 IN X 24.0000 IN X 30.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	24.00 In Width X 12.00 In Depth X 30.00 In Height
------	---

### Descriptions

Description	ENCL 30X24X12 N4X SS CH CLAMP CVR
extra long description	B-LINE 302412-4XS TYPE 4X SSL SGL-D
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure, 30" height, 12" length, 24" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Medium single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Door Enc, 30X24X12
Special Features	Stainless door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051870022
Manufacturers Part Number	3024124XS
UPC	782051870022

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	66.309

## Uses, Certifications, and Standards

Application	Utility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Safety and Security SystemsGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Critical PowerCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Power Distribution and ControlsCommercial / Institutional Buildings / Structures - Commercial/I
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	CSA C22.2.,NEMA,UL 50