



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35154 SQ Shank Screwdriver 1/4 X 4"

Ideal

Catalog Number	35154
Manufacturer	Ideal
Description	Ideal, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 In, Overall Length: 8-3/8 In, Shank Length: 4 In, Handle Type: Cushioned Rubber Grip, Shank Shape: Square, Tip Type: Keystone, Shank Size: 1/4 In, Warranty: Lifetime Guarantee
Weight per unit	0.3333 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	Cushioned Rubber Grip
Shank Length	4
Shank Shape	Square
Tip Size	1/4
tip type	Keystone

Dimensions and Weight

Overall Length	8-3/8
----------------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SQ SHANK SCREWDRIVER 1/4 X 4"
extra long description	IDEAL 35-154 SQ SHANK SCREDR 1 4X4
Features	The Heavy-Duty Square Shaft Keystone Cushioned-Grip Screwdriver features a tough, chrome vanadium steel blade and heavy-duty square shank that offers wrench-assisted turning. Its cushion-grip handle is resistant to oil, gas, and water, and helps to prevent slippage offering greater torque as well as superior comfort. Plate chipping is prevented by a vapor-blasted tip, which is also cross-ground to provide a precise and secure fit in the screw slot. The handle ends are also color-coded for quick and easy id
Long Description	IDEAL, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 IN, Overall Length: 8-3/8 IN, Shank Length: 4 IN, Handle Type: Cushioned Rubber Grip, Shank Shape: Square, Tip Type: Keystone, Shank Size: 1/4 IN, Warranty: Lifetime Guarantee
Product Type	SQ Shank Scredr 1 4X4 In
Special Features	Features: Larger Shank For Heavy-Duty Applications; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Square Shank Models Offer Wrench-Assisted Turning; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grips; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 1/4 IN; Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250351541
Manufacturers Part Number	35154
UPC	783250351541

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Heavy-Duty, Slotted, Keystone Tip

Packaging

Carton	1
Weight Per each	0.3333