ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BIT350 350MCM 2-Entry Term

Burndy LLC

Catalog Number	BIT350
Manufacturer	Burndy LLC
Description	Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 10 Awg-350 Kcmil, Al/Cu Rated.
Weight per unit	0.3000 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	10 AWG-350 KCMIL
Insulation Type	Plastisol
Material	Aluminum
Operating Voltage	600 V

Descriptions

Description	350MCM 2-ENTRY TERM
extra long description	BUR BIT350 350-10 BOTHSIDE,UNITAP
Long Description	Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 10 AWG-350 kcmil, Al/Cu Rated.
Product Type	RUN/TAP
Special Features	Features: Clear Plastisol Covered AL6061-T6 Aluminum Body: Saves Time, Lowers Installation Costs, Eliminates Taping, Clear Plastisol: Allows Visual Confirmation That Conductor Is Properly Inserted, Oxide Inhibitor Pre-Installed: Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking: Reduces Number Of Connectors Carried In Inventory, Torque: 275 IN-LB, Wire Entry: Double, Hex Size (key): 5/16 IN, Conductor Size (run - Range): 10 AWG - 250 KCMIL, Type Of Insulation: Plastisol, Wire

Manufacturer Information

Brand	BURNDY
GTIN	00781810133538
Manufacturers Part Number	BIT350
sub brand	UNITAP
UPC	781810133538

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	BIT

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	60
Weight Per each	0.3

Uses, Certifications, and Standards

Application	For Indoor Use Only, Copper Or Stranded Aluminum
standard	UL 486A-486B
Temperature Rating	90 °C