Specifications

Eaton BRP20B200

Catalog Number: BRP20B200

Plug-on neutral main circuit breaker loadcenter,200A,X5,Aluminum,Cover included,NEMA 1,Metallic,22kAIC,CSR2200,40 circuits,Single pole,20 spaces,Two hots, a neutral and a ground,Single-phase,#6-1/0 AWG Cu/Al,25,Kilo Ampere,25kAIC,Gray,Combi

General specifications

Product Name Eaton BR main breaker loadcenter	Catalog Number BRP20B200
UPC 786689054977	Product Length/Depth 29.12 in
Product Height 3.88 in	Product Width 14.31 in
Product Weight 28.2 lb	Warranty 10 year

Certifications

UL 50

UL 67

Powering Business Worldwide

Product specifications

Special features
Main circuit breaker

Type
Plug-on neutral main circuit breaker loadcenter

Amperage Rating
200 A

Bus material
Aluminum

Cover
Cover included

Main circuit breaker
CSR2200

Number of circuits
40

Number Of Poles
Single-pole

Number of spaces
20

Phase
Single-phase

Wire size
#6-1/0 AWG Cu/Al

Bus Rating
25 kA

Enclosure color
Gray

Mounting
Combination

Used with
Type BR 1-inch breakers

Voltage rating
120/240 V

Box size
X5

Resources

Brochures
Loadcenters and Circuit Breakers

Specifications and datasheets
Eaton Specification Sheet - BRP20B200

Warranty guides
Eaton type BR circuit breaker limited warranty June 2024

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

22 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

25 kAIC

NEMA rating

NEMA 1

Quantity

1

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia