



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35164 RD Shank Screwdr, 1/4 X 4"

*Ideal*

Catalog Number	35164
Manufacturer	Ideal
Description	Ideal, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 In, Overall Length: 8-3/8 In, Shank Length: 4 In, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 1/4 In, Warranty: Lifetime Guarantee
Weight per unit	0.2833 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Type	Cushioned Rubber Grip
Shank Length	4
Shank Shape	Round
Tip Size	1/4
tip type	Keystone

### Material, Color, and Finish

Blade Material	Chrome Vanadium Steel
----------------	-----------------------

### Dimensions and Weight

Overall Length	8-3/8
----------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RD SHANK SCREWDR, 1/4 X 4"
extra long description	IDEAL 35-164 RD SHANK SCREWDR, 1 4X
Features	The Heavy-Duty Round Shaft Keystone Cushioned-Grip Screwdriver has a cushion-grip handle that is resistant to oil, gas and water, and helps to prevent slippage for greater torque and superior comfort. They feature nickel chrome plated vanadium steel heavy-duty square shanks and offer wrench-assisted turning. It has a cross-ground black oxide finish tip to provide a precise and secure fit in the screw slot. The handle ends are all color-coded for quick and easy identification. Screwdriver meets ASTM F1505-0
Long Description	IDEAL, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 IN, Overall Length: 8-3/8 IN, Shank Length: 4 IN, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 1/4 IN, Warranty: Lifetime Guarantee
Product Type	RD Shank Screwdr, 1 4X4 In
Special Features	Features: Larger Shank For Heavy-Duty Applications; Identification Mark On Ends; Vapor-Blasted Tip Prevents Plate Chipping; Precision Ground Tip Provides Secure Fit In Screw Slot; Square-Shank Models Offer Wrench-Assisted Turning; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grips; Shank Size: 1/4 IN; Warranty: Lifetime Guarantee

## Manufacturer Information

Brand	Ideal
GTIN	00783250351640
Manufacturers Part Number	35-164
UPC	783250351640

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Heavy-Duty, Slotted, Keystone Tip

## Packaging

Carton	1
Weight Per each	0.2833