ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



C01045 8 X 10 COMBO MODULE RJ45 W/RJ31X

PASS & SEYMOUR/LEGRAND

Catalog Number	C01045
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	The 10x8 combo distributes up to 4 incoming telephone lines (RJ45) to 10 locations, and 1 GHz video to eight locations. The innovative mounting bracket includes a detachable platform for the coax splitter, allowing easy access to all termination ports
Weight per unit	1.5 (lbs/each)
Product Category	Pwrsuppl-Modules-Network Inter

Features

Number Of Ports	10.0
Connection	RJ31X, F Connector, RJ45

Material, Color, and Finish

Color	Black

Descriptions

Description	8 X 10 COMBO MODULE RJ45 W/RJ31X
Features	The 10x8 combo distributes up to 4 incoming telephone lines (RJ45) to 10 locations, and 1 GHz video to eight locations. The innovative mounting bracket includes a detachable platform for the coax splitter, allowing easy access to all termination ports
Long Description	The 10x8 combo distributes up to 4 incoming telephone lines (RJ45) to 10 locations, and 1 GHz video to eight locations. The innovative mounting bracket includes a detachable platform for the coax splitter, allowing easy access to all termination ports
Product Type	8X10 Combo Module RJ45 W/RJ31X
Extra Long Description	PAS CO1045 8X10 COMBO MODULE RJ45 W

Manufacturer Information

Brand	LEGRAND-ON-Q
	LEGRAND-PASS & SEYMOUR
GTIN	00804428066897
Manufacturers Part Number	CO1045
UPC	785007

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories

Packaging

Carton	1
Package	10
Weight Per Each	1.5 (lbs/each)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Standard	UL, RoHS

CO1045 & CO1110

10x8 Combo Module RJ45 with RJ31X

10x8 Combo Module 110 IDC Punchdown with RJ31X



CONNECT VOICE & VIDEO YOUR WAY

Both the CO1045 and CO1110 distributes up to four lines of phone to 10 locations and 1 GHz digital video to eight locations from a cable company approved Antronix splitter. Like their namesake, the CO1045 terminates to RJ45 ports on the phone module while the CO1110 terminates to 110 Punchdown blocks.

Both modules are UL listed and include a RJ31X line seizure port for home security configuration. The Antronix video splitter exceeds the performance specifications of major cable service providers and its nickel plated housing provides excellent corrosion resistance in even challenging outdoor conditions.

The module ships with all needed corrosion-resistant infrastructure components. To enable easy access to any termination port during installation, the platform for the Antronix video splitter detaches from the telecom bracket. When finished, the attached platform holds tight into a compact form factor, maximizing available space in the enclosure for other components.

FEATURES

- Two connection options: RJ45 or 110 IDC Punchdown
- Voice and video distribution to 10 and eight locations, respectively
- Mounting infrastructure included
- Antronix digital video splitter exceeds cable company requirements
- UL listed
- Simple, convenient installation