ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

C1164 RG62U 95% BRD SHLD

Southwire Company

Catalog Number	C1164
Manufacturer	Southwire Company
Description	Coaxial Cable, RG62A/U Non-Plenum, Ul Awm/CL2 Type; 1000 FT; 0.242 Inch Outer Diameter; Copper Clad Steel Conductor Material; Ul, Etl, Csa Approval; 300 V Voltage Rating; 75 Deg C Temperature Rating; 1 Conductor(S); Polyethylene Insulation Material
Weight per unit	0.0300 (lbs/ft)
Product Category	Coaxial Cable-Non-Plenum

Features

Conductor Construction	SOLID
Conductor Size	22 AWG
Nominal Impedance	93 OHM
Number of Conductors	1
Voltage Rating	300 V

Material, Color, and Finish

Conductor Material	Copper Clad Steel
Insulation Color	NATURAL
Insulation Material	Polyethylene
Jacket Color	BLACK
Jacket Material	PVC
Shield Material	BARE COPPER BRAID

Dimensions and Weight

Length	1000 ft
Outer Diameter	0.242 INCH

Descriptions

Additional Information	ROHS Compliant; Conductor Resistance 42 Ohm/KFt; Capacitance 13.5 Picofarad/Ft
Commodity Description	NON-PLENUM COAXIAL CABLE
Description	RG62U 95% BRD SHLD
Long Description	COAXIAL CABLE, RG62A/U NON-PLENUM, UL AWM/CL2 TYPE; 1000 FT; 0.242 INCH OUTER DIAMETER; COPPER CLAD STEEL CONDUCTOR MATERIAL; UL, ETL, CSA APPROVAL; 300 V VOLTAGE RATING; 75 DEG C TEMPERATURE RATING; 1 CONDUCTOR(S); POLYETHYLENE INSULATION MATERIAL
Product Type	Coaxial Cable

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Cables & Cords
Manufacturers Part Number	920020608
Model	92002

Taxonomies, Classifications, and Categories

Category Description	COAX CABLE
Type	RG62A/U Non-Plenum, UL AWM/CL2

Packaging

Carton	500
Weight Per foot	0.03

Uses, Certifications, and Standards

Approval	UL, ETL, CSA
Temperature Rating	75 DEG C