



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

277/480 VOLTS 277/480 VOLTS
277/480 VOLTS 277/480 VOLTS

44299 Voltage & Conduit Marker, "277/480V", Med, 4/Card

Ideal

Catalog Number	44299
Manufacturer	Ideal
Description	Ideal, Marker Card, Voltage and Conduit, Medium, Size: 1-1/8 In Width, Length: 4-1/2 In, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 Deg F, Text Size: 3/4 In, Adhesion: 45 Oz/In Width Ultimate
Weight per unit	0.0200 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Legend	277/480V
Material	Vinyl-Impregnated Cloth
Number of Markers	20

Dimensions and Weight

Length	4.5
Width	1-1/8

Descriptions

Description	VOLTAGE & CONDUIT MARKER, "277/480V", MED, 4/CARD
extra long description	IDEAL 44-299 WIRE MRKR,277 480V,TYP
Features	Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxesNon-conductive for user safetyHigh-adhesion properties with easy removabilityVinyl-impregnated cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilNon-smear, black legend on bright orange background for high visibilityTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate SELECT PART N
Long Description	IDEAL, Marker Card, Voltage And Conduit, Medium, Size: 1-1/8 IN Width, Length: 4-1/2 IN, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 DEG F, Text Size: 3/4 IN, Adhesion: 45 OZ/IN Width Ultimate
Product Type	Voltage & Conduit Marker, "277/480V", Med, 4/Card
Special Features	Adhesion: 45 OZ/IN Width Ultimate;Features: Identify Junction Boxes, Switches, Circuit Breakers,Raceways, Pipe And Fuse Boxes;High-Adhesion Properties With Easy Removability;Non-Conductive For User Safety;Non-Smear, Black Legend On Bright Orange BackgroundFor High Visibility;Resist Abrasion, Moisture, Dirt And Oil;Temperature Range: -40 DEGF To 180 DEGF (-40 DEGC To 82 DEGC) Adhesion: 45 Oz/IN Width Ultimate;Temperature Range: -40 to 180 DEG F;Text Size: 3/4 IN;Vinyl-impregnated Cloth Construction Provides



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00783250442997
Manufacturers Part Number	44-299
UPC	783250442997

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Voltage And Conduit, Medium

Packaging

Carton	25
Weight Per each	0.02

Uses, Certifications, and Standards

standard	RoHS
----------	------