



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



363610SD Encl 36X36X10 N4 SLD HC, QTR TRN LTCH *Cooper B-Line/Cable Tray*

Catalog Number	363610SD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 10" Length, 36" Width, Nema 4, Hinged Cover, SD Enclosure, Wall Mount, Medium Single Door, Thru Holes, Optional External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	119.4 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

dimensions	10.0000 IN X 36.0000 IN X 36.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	36.00 In Width X 10.00 In Depth X 36.00 In Height
------	---

Descriptions

Description	ENCL 36X36X10 N4 SLD HC,QTR TRN LTCH
extra long description	B-LINE 363610-SD TYPE 4/12 SGL SOLI
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,36" height,10" length,36" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket
Product Type	Type 4/12 SGL Solid Door Enc, 36X36X10
Special Features	1/4 turn latches

Manufacturer Information

Brand	Eaton
GTIN	00782051258820
Manufacturers Part Number	363610-SD
UPC	782051258820

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	119.419

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and ControlsCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherGeneration - Renewable Energy - Alternative EnergyUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Strctures - AftermarketCommercial / Institutional Buildings / Structures - Building Automation and MonitoringDatacenters - IT Space: CI
Mounting	WALL
nema rating	4
standard	CSA C22.2.,UL 50,NEMA