

Eaton 3MM320R

Catalog Number: 3MM320R

Eaton's Three-Phase Residential Meter Stack Module, Group Metering Type, 200A, Aluminum Bus 800 Ampere, No bypass, Outdoor, Five-jaws, 3 Sockets, Three-phase in, single-phase out, Ring Security 120/208V



General specifications

Product Name	Catalog Number
Eaton residential meter stack	3MM320R
UPC	Product Length/Depth
786849052027	54.5 in
Product Height	Product Width
8 in	16 in
Product Weight	Warranty
65 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

Type

Group Metering

Utility approvals

MD : First Energy (Potomac Edison)

AL : Alabama Power

DC : Atlantic City Electric / Delmarva (Connectiv)

DE : Atlantic City Electric / Delmarva (Connectiv)

MD : Atlantic City Electric / Delmarva (Connectiv)

NJ : Atlantic City Electric / Delmarva (Connectiv)

TX : CenterPoint Energy (HL&P/Reliant)

NC : Dominion

VA : Dominion

MI : DTE Energy (Detroit Edison)

NM : El Paso Electric

TX : El Paso Electric

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

TN : Nashville Electric Service

CA : PacifiCorp/Pacific Power/Rocky Mountain Power

ID : PacifiCorp/Pacific Power/Rocky Mountain Power

OR : PacifiCorp/Pacific Power/Rocky Mountain Power

UT : PacifiCorp/Pacific Power/Rocky Mountain Power

WA : PacifiCorp/Pacific Power/Rocky Mountain Power

WY : PacifiCorp/Pacific Power/Rocky Mountain Power

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

IN : Indianapolis Power and Light (IP&L)

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER MODULES, DIMENSIONS, 200A, MM, TMP

Specifications and datasheets

Eaton Specification Sheet - 3MM320R

Interrupt rating

Depends on selected main circuit breaker

Enclosure

Outdoor

Secondary circuit breaker

CCV2_X, CCVH2_X, CVS2_XMM, CV2_XMM, CVH2_XMM

Bus Rating

800 A

Phase

Three-phase in, single-phase out

Voltage rating

120/208V

Amperage Rating

200A

Bus material

Aluminum

Bypass

None

Number of jaws

Five-jaw

Number of sockets

3

Phase balance

A-B

Security

Ring