

# Eaton 3MM512R

Catalog Number: 3MM512R

Eaton's Three-Phase Residential Meter Stack Module, Group Metering Type, 125A, Aluminum Bus 800 Ampere, No bypass, Indoor/outdoor, Five-jaws, 5 Sockets, Three-phase in, single-phase out, Ring Security, 120/208V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton residential meter stack	3MM512R
<b>UPC</b>	<b>Product Length/Depth</b>
786849051990	55.5 in
<b>Product Height</b>	<b>Product Width</b>
8 in	15 in
<b>Product Weight</b>	<b>Warranty</b>
65 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Group Metering

### Utility approvals

DC : Atlantic City Electric / Delmarva (Connectiv)

DE : Atlantic City Electric / Delmarva (Connectiv)

MD : First Energy (Potomac Edison)

MD : Atlantic City Electric / Delmarva (Connectiv)

NJ : Atlantic City Electric / Delmarva (Connectiv)

TX : CenterPoint Energy (HL&P/Reliant)

NC : Dominion

VA : Dominion

MI : DTE Energy (Detroit Edison)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

TN : Nashville Electric Service

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

IN : Indianapolis Power and Light (IP&L)

WA : Puget Sound Energy

WA : Tacoma Public Utilities

### Interrupt rating

Depends on selected main circuit breaker

### Enclosure

Indoor/outdoor

### Secondary circuit breaker

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER MODULES, DIMENSIONS, 125A, MM, TMP

### Specifications and datasheets

Eaton Specification Sheet - 3MM512R

BR2\_, BRH2\_, BRHH2\_

Bus Rating

800 A

Phase

Three-phase in, single-phase out

Voltage rating

120/208V

Amperage Rating

125A

Bus material

Aluminum

Bypass

None

Number of jaws

Five-jaw

Number of sockets

5

Phase balance

A-B

Security

Ring



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)