Specifications

Eaton CHP22N125X2

Catalog Number: CHP22N125X2

Eaton CH PON 3/4-inEaton CH loadcenter, 125A, convertible, 22 spaces

General specifications

Product Name	Eaton CH convertible loadcenter
Catalog Number	CHP22N125X2
UPC	786679189726
Product Length/Depth	21 in
Product Height	3.88 in
Product Width	14.31 in
Product Weight	11.5 lb
Warranty	Limited lifetime
Certifications	UL 50 UL 67
Catalog Notes	Purchase Size X2 Cover Separately

Powering Business Worldwide

Product specifications

Type
Convertible

Amperage Rating
125 A

Bus material
Copper

Cover
X2

Feed type
Top/bottom

Number of circuits
22

Number of spaces
22

Phase
Single-phase

Voltage rating
120/240 V

Box size
X2

Enclosure
NEMA 1

Enclosure material
Metallic

Interrupt rating
10 kAIC

Number of wires
3

Resources

Brochures
Loadcenters and Circuit Breakers

Multimedia
AFCI Educational Video

Specifications and datasheets
Eaton Specification Sheet - CHP22N125X2

Warranty guides
Eaton type CH circuit breaker limited warranty June 2024

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia