ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1701 North Jackson
McAllen, TX 78501-0000
Phone: 9563312410
Fax: 9563312411



CHQ115 TYPE CHQ CLASSIFIED BRKR 15A/1 POLE 120/240V 10K

EATON CORP

Catalog Number	CHQ115
Manufacturer	EATON CORP
Description	Standard Trip Circuit Breaker, 15 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-On, 120/240 V ac, 3 in Overall Height, 2.5 in Overall Length, 0.8 in Overall Width, 0.30 lb
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

Poles	Single-pole
Voltage Rating	120/240 V
Dimensions	0.7000 IN X 3.0000 IN X 2.7000 IN
Interrupt Rating	10

Descriptions

Description	TYPE CHQ CLASSIFIED BRKR 15A/1 POLE 120/240V 10K
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	3/4" Thermal magnetic circuit breakers,Type CHQ 3/4-Inch classified replacement breaker,15 A,10 kAIC,Single-pole,120/240V,CHQ,(1) #14-8 AWG, (2) #14-10 AWG Cu/Al,CHQ,Type CH Loadcenters
Product Type	CHQ Classified 15A/1 Pole 120/240V 10K
Extra Long Description	ETN CHQ115 CHQ Classified 15A/1 Pol

Manufacturer Information

Brand	EATON CUTLER-HAMMER
	Eaton
GTIN	00782113010816
UPC	782112

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers

Packaging

Carton	1
Package	10
Weight Per Each	0.3000 (lbs/each)

1701 North Jackson
McAllen, TX 78501-0000
Phone: 9563312410
Fax: 9563312411

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherDatacenters - IT Space: CI and Hyper Converged
Standard	UL 489

Product specifications

Eaton CHQ115

Catalog Number: CHQ115

3/4" Thermal magnetic circuit breakers,Type CHQ 3/4-Inch classified replacement breaker,15 A,10 kAIC,Single-pole,120/240V,CHQ,(1) #14-8 AWG, (2) #14-10 AWG Cu/Al,CHQ,Type CH Loadcenters



General specifications

Product Name
Eaton Classified 3/4" thermal magnetic circuit breaker

Catalog Number
CHQ115

UPC
782113010816

Product Length/Depth
0.7 in

Product Height
2.7 in

Product Width
3 in

Product Weight
0.25 lb

Warranty
Limited lifetime residential, 1 year commercial

Certifications
UL 489

Catalog Notes
Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type CHQ 3/4-Inch classified replacement breaker

Amperage Rating

15 A

Voltage rating

120/240 V

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHQ

Wire size

(1) #14-8 AWG
(2) #14-10 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

Loadcenters and Circuit Breakers

Standard circuit breaker catalog numbers - 5651B63SH09

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHQ115

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia