



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5P1500RT 7161 Eaton Nema 1.5K 120/120V No Ebm *Eaton Power Quality*

Catalog Number	5P1500RT
Manufacturer	Eaton Power Quality
Description	Eaton 5P Ups, 1440 Va, 1440 W, 5-15P Input, Outputs: (8) 5-15R, 120V
Weight per unit	72.7 (lbs/each)
Product Category	Uninterruptible Power Supplies

### Features

accessories	Tower pedestals, Quick Start Guide, Phillips head screw driver
battery	Sealed, lead-acid
Battery Type	VRLA
dimensions	20.6000 IN X 17.4000 IN X 3.4000 IN
Voltage Rating	151/153 V
Wattage	1,440 W

### Dimensions and Weight

Height	3.4 in
Length	20.6 MM
Width	3010-2

### Descriptions

Description	7161 EATON NEMA 1.5K 120/120V NO EBM
extra long description	ETN 5P1500RT EATON 5P RACKMOUNT 2U
Features	The Eaton 5P UPS delivers reliable backup power in tower and various rackmount form factors for enterprise and distributed IT applications. As the first in the UPS industry to comply with the UL 2900-2-2 cybersecurity standard, Eaton's optional gigabit network card (NETWORK-M2) provides remote monitoring and management for the 5P family of products. When paired with Eaton Intelligent Power Manager (IPM) software, IT professionals can seamlessly manage their connected equipment install base, even in virtual
Long Description	Eaton 5P UPS, 1440 VA, 1440 W, 5-15P input, Outputs: (8) 5-15R, 120V
Product Type	Eaton 5P Rackmount 2U Ups

### Manufacturer Information

Brand	Eaton
GTIN	00743172039620
Manufacturers Part Number	5P1500RT
UPC	743172039620



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description.....SURGE SUPRESSION PRODUCTS

Type.....UPS

## Packaging

Carton.....1

Weight Per each.....72.68

## Uses, Certifications, and Standards

Application.....Backup Power and Electronic Power Conversion

Frequency Rating.....40/50/60

standard.....UL 1778; UL497A; cUL Listed; FCC Part 15 subpart B Class A