ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

ET1705C 7DAY 30A SPST Time Switch

Intermatic Inc.

Catalog Number	ET1705C
Manufacturer	Intermatic Inc.
Description	7-Day 1-Circuit Electronic Control, 120-277 Vac, SPST, Indoor Metal Enclosure
Weight per unit	2.9 (lbs/each)
Product Category	Electronic Time Switches

Features

action	1 x SPST
amperage rating	30
connection	Teeter Type
Contact Configuration	1 NO
Contact Rating	30 AMP @ 120/240 VAC (Resistive NO), 20 AMP @ 28 VDC (Resistive NO), 30 AMP @ 120/240 VAC (Inductive NO), 5 AMP @ 120/240 VAC (Tungsten NO), 20 AMP @ 120 - 277 VAC (Ballast NO)
motor power	1 HP @ 120 VAC (NO), 2 HP @ 240 VAC (NO)
Poles	1
Timing Range	1 MIN - 6 DAYS 23 HR 59 MIN
Voltage Rating	120 to 277

Descriptions

Description	7DAY 30A SPST TIME SWITCH
extra long description	INT-MAT ET1705C 7-Day 1-Circuit Ele
Features	This series offers an easy way to upgrade from a basic mechanical time switch to an electronic time switch. These timers will allow for up-to-the-minute programming, battery backup for power loss, up to 28 events total, and automatic daylight saving time corrections without the need of user interaction. They come in standard 24-hour, 7-day and 7-day astronomic versions.
Long Description	7-Day 1-Circuit Electronic Control, 120-277 VAC, SPST, Indoor Metal Enclosure
Product Type	7-Day 1-Circuit Electronic Control, 120-277 Vac, SPST, Indoo
Special Features	Features: 7-Day, Multi-Voltage, Battery Backup, 1 Year Warranty, Automatic Adjustment for Daylight Saving Time

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275109841
Manufacturers Part Number	ET1705C
UPC	078275109841

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	ELECTRONIC

Packaging

Carton	1
Package	6
Weight Per each	2.917

Uses, Certifications, and Standards

Application	Indoor, HVACR, Industrial
Enclosure	NEMA 1 Steel
Frequency Rating	50/60
Mounting	WALL MOUNT
Operating Temperature	-40 to +155 DEG F, -40 to +68 DEG C
standard	cCSAus Certified, California TITLE 24 Compliant, HVACR, Title CA 20 Listed