ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F032735EC0 32W T8 48" 3500K 75 Cri Bi-Pin Energy Saving

Sylvania-Ledvance

Catalog Number	F032735EC0
Manufacturer	Sylvania-Ledvance
Description	Lamp, Magnetic Rapid Start; 32 W; 48 Inch Nominal Length; Shape Designation T8; Style 735 Octron 700; Medium 2 Pin Base; Initial Intensity 2800 Lumen; Color Rendering Index 75; Color Temperature 3500 K; Life 20000 HR; Standard Package 30
Weight per unit	0.4936 (lbs/each)
Product Category	20000522161328

Features

Initial Intensity	2800 LUMEN
Nominal Length	48 INCH
Wattage	32 W

Material, Color, and Finish

Base Type	Medium 2 Pin
Color Rendering Index	51898
Color Temperature in Kelvin	3500 K
Style	735 OCTRON 700

Descriptions

Additional Information	APPLICABLE STANDARD ANSI, IEC, IES; APPLICATION CONFERENCE ROOM, HOTEL, LOBBY, MOTEL, OFFICE, RESIDENTIAL, SHOP, SHOWROOM, SUPER MARKET; CONSTRUCTION STANDARD TUBE
Commodity Description	LINEAR FLUORESCENT STRAIGHT LAMPS
Description	32W T8 48" 3500K 75 CRI BI-PIN ENERGY SAVING
Long Description	LAMP, MAGNETIC RAPID START; 32 W; 48 INCH NOMINAL LENGTH; SHAPE DESIGNATION T8; STYLE 735 OCTRON 700; MEDIUM 2 PIN BASE; INITIAL INTENSITY 2800 LUMEN; COLOR RENDERING INDEX 75; COLOR TEMPERATURE 3500 K; LIFE 20000 HR; STANDARD PACKAGE 30
Product Type	Linear Fluorescent Lamp

Manufacturer Information

Brand	OSRAM SYLVANIA
Manufacturers Part Number	FO32/735/ECO

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	MAGNETIC RAPID START

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Standard Package	30 A
Weight Per each	0.4936