ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F032741EC0SL FLR Lamp

Sylvania-Ledvance

Catalog Number	F032741EC0SL
Manufacturer	Sylvania-Ledvance
Description	Shatter Resistant Coated Lamp, 32 W; 48 Inch Nominal Length; Shape Designation T8; Medium Bipin Base; Initial Intensity 2715 Lumen; Color Rendering Index 78; Color Temperature 4100 K; Life 24000 (3 HR Start), 28000 (12 HR Start) HR; Standard Package 30
Weight per unit	0.4500 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

Initial Intensity	2715 LUMEN
Initial Intensity in Lumen	2715 K
Nominal Length	48 INCH
Nominal Length in inch	72513
Wattage	32 W

Material, Color, and Finish

Base Type	MEDIUM BIPIN
Color Rendering Index	78 WTT
Color Temperature in Kelvin	30 Amp at 120/240 Volt AC, 25 Amp at 277 Volt AC/12.5 Amp at 480 Volt AC (Non-Conductive)

Descriptions

Commodity Description	SHATTER RESISTANT FLUORESCENT LAMPS
Description	FLR LAMP
Long Description	SHATTER RESISTANT COATED LAMP, 32 W; 48 INCH NOMINAL LENGTH; SHAPE DESIGNATION T8; MEDIUM BIPIN BASE; INITIAL INTENSITY 2715 LUMEN; COLOR RENDERING INDEX 78; COLOR TEMPERATURE 4100 K; LIFE 24000 (3 HR START), 28000 (12 HR START) HR; STANDARD PACKAGE 30
Product Type	Shatter Resistant Fluorescent Lamp

Manufacturer Information

Brand	OSRAM SYLVANIA INC.
Manufacturers Part Number	F032741EC0SL

Taxonomies, Classifications, and Categories

Category Description	Fluorescent

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Standard Package	30 A
Weight Per each	0.45