ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F17T8SP41EC0 17W T8 24" 4100K 78 Cri Bi Pin Energy Saving

Ge By Current Lamps

Catalog Number	F17T8SP41EC0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, G13 Medium Bi-Pin Base, T8 Bulb Shape, 78, 30000 H Average Life, 4100 K, 70 V, 17 W, 1325 LM Brightness (Lumens), Soda Lime Housing Material, 1.0 In Diameter, 24.0 In Length, Instant;Rapid, 0.26 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	1325
Wattage	17

Material, Color, and Finish

color rendering index (cri)	78.0

Descriptions

Description	17W T8 24" 4100K 78 CRI BI PIN ENERGY SAVING
extra long description	GEL F17T8/SP41/ECO 45748 FLUORESCEN

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168457484
UPC	043168457484

Taxonomies, Classifications, and Categories

Category Description	Fluorescent

Packaging

Carton	1
Package	24
Weight Per each	0.26