



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



56334 Steel Fish Tape, 1/8" X 240-Foot

Klein Tools

Catalog Number	56334
Manufacturer	Klein Tools
Description	The Klein Tools' 240-Foot High Carbon Steel Fish Tape Is Perfect For Wire Runs Associated With Commercial, Residential and Voice-Data-Video Installations. The Optimized Housing and Handle Design Decreases Payout Effort and Reduces Binding. A Multiple-Position Handle Allows For A Firm, Steady Grip As You Pull or Rewind The Tape. The Unique Interior Case Shape Combines The Leverage Of Square Cases and The Comfort Of Round Cases, Which Makes Rewinding Tape After A Long Run Easier. The Tape Features Laser-Etch
Weight per unit	7.9 (lbs/each)
Product Category	20191120151652

Features

Material	Steel
media	Yes
Overall Height	16.21" (41.2 cm)
Overall Width	12.35" (31.4 cm)
tape end	Double Loop Steel
Tape Size	240' x 1/8" x 0.062" (73.2 m x 0.3 cm x 0.2 cm)
Tensile Strength	—

Material, Color, and Finish

Color	Orange/Black
-------	--------------

Dimensions and Weight

Diameter	13" (33 cm)
Overall Length	1.85" (4.7 cm)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	STEEL FISH TAPE, 1/8" X 240-FOOT
extra long description	KLEIN 56334 240' Steel Fish Tape
Features	The Klein Tools' 240-Foot High Carbon Steel Fish Tape is perfect for wire runs associated with commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. A multiple-position handle allows for a firm, steady grip as you pull or rewind the tape. The unique interior case shape combines the leverage of square cases and the comfort of round cases, which makes rewinding tape after a long run easier. The tape features laser-etch
Long Description	The Klein Tools' 240-Foot High Carbon Steel Fish Tape is perfect for wire runs associated with commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. A multiple-position handle allows for a firm, steady grip as you pull or rewind the tape. The unique interior case shape combines the leverage of square cases and the comfort of round cases, which makes rewinding tape after a long run easier. The tape features laser-etch
Product Type	240' Steel Fish Tape
Special Features	Optimized Housing Design, High Carbon Steel

Manufacturer Information

Brand	Klein Tools
GTIN	00092644563348
Manufacturers Part Number	56334
UPC	092644563348

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Steel Fish Tape

Packaging

Carton	1
Package	5
Weight	7.9 lb (3.6 kg)
Weight Per each	7.88

Uses, Certifications, and Standards

Application	Wire Pulling
standard	—