ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

GAL445 4", 45D RGD Elb

Robroy/Ecn Korns

Catalog Number	GAL445
Manufacturer	Robroy/Ecn Korns
Description	Standard Radius Elbow, 4 In Trade Size, Hot Dip Galvanized, 45 ° Connection Orientation, 16 In Bend Radius, External Threaded Connection, 2691 LB/100
Weight per unit	26.9 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1
Bend Angle	45 DEG
End Type	EXTERNAL THREADED
Material	Steel
Trade Size - Fractional	4

Descriptions

Also Known As...	Sweep
	Elbow Pre-Fab
Commodity Description	ELBOWS-COUPLINGS-NIPPLES - STEEL
Description	4",45D RGD ELB
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US), UL 6, CSA C22.1/C22.2, NOM APPROVAL; ANSI/NFPA 70, NEC 344, ISO 9001 APPLICABLE STANDARD; BULK STANDARD PACKAGE; 4 INCH TRADE SIZE; EXTERNAL THREADED END TYPE; 45 DEGREE BEND ANGLE; 16 INCH BEND RADIUS; APPLICATION INDOOR/OUTDOOR; GALELB MODEL

Manufacturer Information

Brand	EC-KORNS
GTIN	00784011001903
Model	GALELB
UPC	784011001903

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	STANDARD RADIUS

Trade Size

Trade Size in inch	4

Availability

Status	Inactive

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Standard Package	BULK
Weight Per each	26.91

Uses, Certifications, and Standards

Approval	UL 6, CSA C22.2