



Catalog Number: 666-SC1
Item Description: N1 SCREW COVER ENCL
UPC Code: 784572108189


Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

Technical drawing of the back panel of the device, showing dimensions and mounting details:



- Overall width: 6.00
- Overall height: 6.00
- Mounting holes (horizontal spacing): 4.13
- Mounting holes (vertical spacing): 4.00
- Mounting holes (4 places): $\varnothing 28$
- Grounding emboss
- Internal components (1, 2, 4) are indicated by dashed lines and arrows.
- Note: (APPLY INSIDE BACK)



6.00

1/2, 3/4 CONC. K.O.
(4 PLACES)

3/4, 1 CONC. K.O.
(2 PLACES)

Material:		16 GA. GALV. STEEL		 MILBANK MANUFACTURING CO.		General Offices: Kansas City, MO	
Finish:		SEE CHART					
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X° ±2°		Third Angle  Projection		Title: 666 SCREW COVER TYPE 1 ENCLOSURE			
				Catalog No.: (SEE CHART)			
				Customer: MILBANK STANDARD			
Scale: NTS		Checked By:		Drawing No.: 1003060			
Drawn By: DY		Approved By:		Date: 04/26/01 Sheet 1 of 1			

NEMA DWG.: #124



Catalog Number: 666-SC1
Item Description: N1 SCREW COVER ENCL
UPC Code: 784572108189

Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

6.00

4.13 MOUNTING HOLES

6.00

4.00 MOUNTING HOLES


GROUNDING EMBOSS

Ø 28 MOUNTING HOLE (4 PLACES)

1

2



4 (APPLY INSIDE BACK)



6.00

1/2, 3/4 CONC. K.O.
(4 PLACES)

3/4, 1 CONC. K.O.
(2 PLACES)

Material:		16 GA. GALV. STEEL		 MILBANK MANUFACTURING CO.		General Offices: Kansas City, MO	
Finish:		SEE CHART					
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X° ±2°		Third Angle  Projection		Title: 666 SCREW COVER TYPE 1 ENCLOSURE			
				Catalog No.: (SEE CHART)			
				Customer: MILBANK STANDARD			
Scale: NTS		Checked By:		Drawing No.: 1003060			
Drawn By: DY		Approved By:		Date: 04/26/01 Sheet 1 of 1			

NEMA DWG.: #124