ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

GT2UMV 2X2 2LMP Static Lensed Troffer, Elec Ballast

Lithonia Lighting

Catalog Number	GT2UMV
Manufacturer	Lithonia Lighting
Description	Lensed Troffer, U Lamp Bulb Shape, 48 In Length, 24 In Width, 3-1/8 In/7.9 CM Height, 120 to 277 V, 32 W, Electronic Ballast, Instant, White, 2600 LM Brightness (Lumens), Bi-Pin Base, 2 Lamps, 1 Ballasts, Steel Housing Material, Baked White Enamel, Recessed Mount, 12.2 LB/Ea
Weight per unit	12.5 (lbs/each)
Product Category	Fluorescent Recessed Architect

Features

Hardware	Yes
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	2
pallet quantity	56
Power Source	Hardwired
Shape	Rectangular
Socket Type	Bi-pin: Single
Warranty	2
Wattage	124

Material, Color, and Finish

Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Descriptions

Description	2X2 2LMP STATIC LENSED TROFFER,ELEC BALLAST
extra long description	LITH GT2U MV Lensed Troffer, 2x2, M

Manufacturer Information

GTIN	00745975081967
UPC	745975081967

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Troffer

Trade Size

aperture size	2x2

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	12.53

Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	UL