Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

ICN3P32N35I 120-277V Elec Bal

Advance By Signify

Catalog Number	ICN3P32N35I
Manufacturer	Advance By Signify
Description	Fluorescent Ballast, Instant, 32 W, 277 V Ac, 0.71 A, Non Dimmable, 3 Lamps, 9.5 In Length, 1.3 In Width, 1 In Height, 0.88 Ballast Factor, 0.98 Power Factor, 50 HZ;60 HZ, Metal Housing Material, 10 % Total Harmonic Distortion, 0.441 KG/Ea
Weight per unit	0.8600 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

Ballast Type	Electronic Fluorescent
Lamp Type	T8

Descriptions

Description	120-277V ELEC BAL
extra long description	ADV 109108 ELE BALLAST (3) F32T8 12

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087091494
Manufacturers Part Number	109108
UPC	781087091494

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST

Packaging

Carton	1
Package	10
Weight Per each	0.86

Uses, Certifications, and Standards

standard	CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;NOM certificate;RoHS Compliant