ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



KA34U 4-500 CU/AL 1 CONDUCTOR LUG

BURNDY LLC

Catalog Number	KA34U
Manufacturer	BURNDY LLC
Description	Conductor Lug, #4 AWG (Stranded) Conductor Size, 500 kcmil (Stranded) Conductor Size, Non-Insulated, Copper/Aluminum Conductor Material, 1 conductor, +194 °F Operating Temperature, 2.81 in Overall Length, Screw Terminal
Weight per unit	0.2800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number Of Conductors	1
Pallet Quantity	4608

Descriptions

Description	4-500 CU/AL 1 CONDUCTOR LUG
Long Description	Aluminum Universal Terminal, 1 Hole, 4 AWG (Str)-500 kcmil, 3/8" Stud, 1 Screw, Al/Cu Rated, Tin Plated.
Product Type	Terminal
	4STR-500 Dual Rated
Special Features	Features: These Dual-Rated One-Conductor Lugs Are Constructed From High Strength Aluminum Alloy And Electro Tin-Plated To Provide Low Contact Resistance, Number Of Screws: 1, Stud/bolt Hole Size: 3/8 IN, Dimension D: 1.5 IN, Dimension N: 0.88 IN, Dimension T: 0.31 IN, Set Screw Type: Allen Key, Installation Torque: 500 IN-LB, Width: 1.51 IN, Height: 1.58 IN, Length: 2.81 IN
Extra Long Description	BUR KA34U 4STR-500 DUAL RATED

Manufacturer Information

Brand	Burndy-US, a Hubbell affiliate
	BURNDY
GTIN	00781810370247
UPC	781810

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Bolted Lugs & Terminals

Packaging

Carton	12
Weight Per Each	0.2800 (lbs/each)


2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	For Aluminum And Copper Conductors
Temperature Rating	194
Standard	UL 486A-486B

On Line Catalog





BURNDY Catalog Number	KA34U
UPC Number	7818103702477
Description	4STR-500 DUAL RATED
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Width (in)	1.51
Length (in)	2.81
Bolt Hole Size (in)	0.38
Thickness	0.31
D - in	1.50
Pad Width (in)	1.52
N (in)	0.88
General	
Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 4 AWG (Str)-500 kcmil, 3/8" Stud, 1 Screw, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	4 STR- 500 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4 AWG-500 kcmil
Physical	
Installation Torque	500
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	3/8
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175