

# LED step light

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



7739W

## Description

120V/AC  
60Hz

## Design features

- Fits into a standard junction box for easy installation (single-gang, handy box, 2" minimum inside width)
- 6 LED's with 6000-6500K light temperature
- Energy-efficient 40,000 hour rated LED lamp light
- Back & side wire, #14 - #12 AWG
- Perfect for any area where low level lighting or safe way-finding is needed, such as hallways, stairways, lobbies, auditoriums and theaters
- Includes vertical and horizontal louvered wallplates

**Table 1. LED Step Light**

Catalog No.	Description	Rating V/AC	Color Suffix
□ 7739__	3W LED Step Light (vertical & horizontal)	120 V/AC, 60Hz	A, LA, W

**Compliances, specifications and availability are subject to change without notice.**



*Powering Business Worldwide*

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Table 2. Specifications

Catalog No.	7739 Series
<b>Series Type</b>	<b>LED Step Light</b>
<b>Illumination</b>	6 LEDs LED life rated 40,000 hours
<b>Color Temperature</b>	6000-6500K
<b>Power Consumption</b>	< 3 Watts
<b>Testing &amp; Code Compliance</b>	cULus Listed UL 1598 and UL8750
<b>Power Supply</b>	120 V/AC, 60 Hz
<b>Installation</b>	Single-gang junction box

Table 3. Materials


Catalog No.	7739 Series
<b>Wallplate</b>	Polycarbonate/ABS
<b>Bottom Housing</b>	Polycarbonate
<b>Strap</b>	Galvanized steel
<b>Termination Accommodations</b>	#14-#12 AWG

Table 4. Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), LA (Light Almond), W (White)

<b>A</b>	<b>LA</b>	<b>W</b>
Almond	Lt. Almond	White

## Certifications & Compliances

Catalog No.	
7739	•

**KEY:**  cULus

Compliances, specifications and availability are subject to change without notice.

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/wiringdevices

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/wiringdevices

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. TD610061EN  
August 2017

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlan Km 17.8 s/n  
Col. Villa Jardin esq.  
Cerrada 8 de Mayo  
Cuautitlan, Mexico CP 54800  
Mexico  
Eaton.mx  
Eaton.com/wiringdevices

Eaton is a registered trademark.

All other trademarks are property  
of their respective owners.

# LED step light

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:



7739W

## Description

120V/AC  
60Hz

## Design features

- Fits into a standard junction box for easy installation (single-gang, handy box, 2" minimum inside width)
- 6 LED's with 6000-6500K light temperature
- Energy-efficient 40,000 hour rated LED lamp light
- Back & side wire, #14 - #12 AWG
- Perfect for any area where low level lighting or safe way-finding is needed, such as hallways, stairways, lobbies, auditoriums and theaters
- Includes vertical and horizontal louvered wallplates

**Table 1. LED Step Light**

Catalog No.	Description	Rating V/AC	Color Suffix
□ 7739__	3W LED Step Light (vertical & horizontal)	120 V/AC, 60Hz	A, LA, W

**Compliances, specifications and availability are subject to change without notice.**



*Powering Business Worldwide*

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Table 2. Specifications

Catalog No.	7739 Series
<b>Series Type</b>	<b>LED Step Light</b>
<b>Illumination</b>	6 LEDs LED life rated 40,000 hours
<b>Color Temperature</b>	6000-6500K
<b>Power Consumption</b>	< 3 Watts
<b>Testing &amp; Code Compliance</b>	cULus Listed UL 1598 and UL8750
<b>Power Supply</b>	120 V/AC, 60 Hz
<b>Installation</b>	Single-gang junction box

Table 3. Materials


Catalog No.	7739 Series
<b>Wallplate</b>	Polycarbonate/ABS
<b>Bottom Housing</b>	Polycarbonate
<b>Strap</b>	Galvanized steel
<b>Termination Accommodations</b>	#14-#12 AWG

Table 4. Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: A (Almond), LA (Light Almond), W (White)

<b>A</b>	<b>LA</b>	<b>W</b>
Almond	Lt. Almond	White

## Certifications & Compliances

Catalog No.	
7739	•

**KEY:**  cULus

Compliances, specifications and availability are subject to change without notice.

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/wiringdevices

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/wiringdevices

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. TD610061EN  
August 2017

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlan Km 17.8 s/n  
Col. Villa Jardin esq.  
Cerrada 8 de Mayo  
Cuautitlan, Mexico CP 54800  
Mexico  
Eaton.mx  
Eaton.com/wiringdevices

Eaton is a registered trademark.

All other trademarks are property  
of their respective owners.