ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



L1030R TURNLOK RECP 3W 30A 125/250V

PASS & SEYMOUR/LEGRAND

Catalog Number	L1030R
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	Turnlok Registered Single Receptacle 3-Wire 30A 125/250V
Weight per unit	0.2452 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

Number Of Wires	3
Outlet Type	Locking
Phase	3
Poles	3-way
Voltage	125/250 V
Voltage Rating	125/250
Wall Plate Included	NO
Wire Size	14 - 10
Amperage Rating	20
Indoor/Outdoor	Indoor

Dimensions and Weight

Size	3.3"

Descriptions

Description	TURNLOK RECP 3W 30A 125/250V
Features	Turnlok Registered Single Receptacle 3-Wire 30A 125/250V
	Impact Resistant, Brass Mounting Strap
Long Description	Turnlok Registered Single Receptacle 3-Wire 30A 125/250V
Product Type	Turnlok Receptacle 3W 30 A125/250V
Special Features	Turnlock, locking device, quick thread assembly, rounded back contour, impact & corrosion resistant, new design external cord grips
Extra Long Description	PAS L1030R TURNLOK RECEPTACLE 3W 30

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007103052
Manufacturers Part Number	L1030R
	L1030-R
UPC	785007

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Turnlock Receptacle

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Trade Size

Amperage	30.0

Packaging

Carton	1
Package	50
Weight Per Each	0.2452 (lbs/each)

Uses, Certifications, and Standards

Application	Commercial
Nema Rating	L10-30R
Standard	CULUS, UL 498

Pass and Seymour
Turnlok® Receptacle 3W 30A 125V/250V
Part No. L1030R



Turnlok® Single Receptacle 3-Wire 30A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

Face color coding by voltage facilitates locating and mating of proper devices.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Side and external screw-pressure-plate back wire capability.

Accepts #14 - #10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007103052	Country Of Origin	Mexico
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	3.48 in

Product Height US	1.28 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	30 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L10-30R
Wire Connection Type	Screw Terminals	Voltage	125/250 V