



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050



885TRBK Radiant 15A 125V TR Duplex Recept BK

Pass & Seymour/Legrand

Catalog Number	885TRBK
Manufacturer	Pass & Seymour/Legrand
Description	Take A Step Up From The Standard. This Tamper-Resistant Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant Registered For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1408 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

gang	1
indoor/outdoor	Indoor
insulation	False
media	Yes
Mounting Type	Box
Number of Wires	3
orientation	Vertical
Outlet Type	Straight Blade, Tamper-Resistant
Poles	2
Voltage	125.0 V, 120.0 V
Wall Plate Included	NO

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	4.2"
Thickness	1.3"



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Descriptions

Description	RADIANT 15A 125V TR DUPLEX RECP BK
extra long description	P&S 885TRBK RADIANT 15A/125V TR DUP
Features	Decorator Style
Long Description	Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Product Type	Radiant 15A/125V TR Dup Recep BK
Special Features	Tamper resistant, quick loop wire aid, extra long strap, side access, push wire

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007861044
Manufacturers Part Number	885-TRBK
UPC	785007861044

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Package	200
Weight Per each	0.1408

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	95% (relative humidity, non-condensing)
Mounting	WALL
nema rating	15A
standard	UL, CULUS, UL 498