



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **886RHC Encl 8X8X6 N3R SM CH** *Cooper B-Line/Cable Tray*

Catalog Number	886RHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Type 3/3R Panel Enclosures, 8" Height, 6" Length, 8" Width, Nema 3R, Hinged Cover, RHC Enclosure, Wall Mount, Small Single Door, 4 Bottom Knockouts, External Mounting Feet, Carbon Steel
Weight per unit	6.8 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

### **Features**

Cable Entry	Knockouts
dimensions	6.0000 IN X 8.0000 IN X 8.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### **Material, Color, and Finish**

Color	ANSI 61 GRAY
-------	--------------

### **Dimensions and Weight**

Size	8.00 In Width X 6.00 In Depth X 8.00 In Height
------	--

### **Descriptions**

Description	ENCL 8X8X6 N3R SM CH
extra long description	B-LINE 886 RHC N3R HC ENC 8X8X6
Features	Eaton's B-Line series panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series Type 3/3R panel enclosures, 8" height, 6" length, 8" width, NEMA 3R, Hinged cover, RHC enclosure, Wall mount, Small single door, 4 bottom knockouts, External mounting feet, Carbon steel
Product Type	N3R HC Enc 8X8X6
Special Features	Rain hood,cont. piano hinge, pull drawn catch

### **Manufacturer Information**

Brand	Eaton
GTIN	00782051143256
Manufacturers Part Number	886 RHC
UPC	782051143256

### **Taxonomies, Classifications, and Categories**

Category Description	STEEL JUNCTION BOXES
Type	Type 3/3R panel enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	6.8

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Power Distribution and ControlsMobile Machinery and Equipment - Mobile Machinery and Equipment - OtherCommercial / Institutional Buildings / Structures - Building Automation and MonitoringCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherRail and
Mounting	EXTERNAL FEET, WALL
nema rating	3R
standard	CSA C22.2, UL 50, NEMA