ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED12A19DIM0850U 12W Led A19 50K Dim 1100LM

Sylvania-Ledvance

Catalog Number	LED12A19DIM0850U
Manufacturer	Sylvania-Ledvance
Description	Led A19, 12W, Dimmable, 80CRI, 1100 Lumen, 5000K, 15000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.3270 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	15000
Base	E26 Medium
dimmable	Yes
Lamp Type	LED A19
lumens	1,100
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	12.00

Material, Color, and Finish

color rendering index (cri)	80
color temperature	5000
Style	A-shape

Dimensions and Weight

Size	2.36

Descriptions

Description	12W LED A19 50K DIM 1100LM
extra long description	SYL LED12A19DIMO850URP/74690 LED12A
Long Description	LED A19, 12W, Dimmable, 80CRI, 1100 Lumen, 5000K, 15000 Life, E26 Medium Base, FROSTED Finish
Product Type	LED12A19DIMO850URP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135746901
Manufacturers Part Number	LED12A19DIMO850URP/74690
sub brand	Ultra
UPC	046135746901

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.327

Uses, Certifications, and Standards

standard	cULus