ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED12BR30D27K 12W Led BR30 Dim 27K

Technical Consumer Prod.

Catalog Number	LED12BR30D27K
Manufacturer	Technical Consumer Prod.
Description	Led Lamp, BR30 Shape, 110 ° Beam Angle, 80, 2700 K, 850 LM Brightness (Lumens), 12 W, 120 V Ac, White, 25000 H Average Life, E26 Base, Dimmable, 3.8 In Diameter, 5.4 In Length, 0.9 Power Factor, -30 °C Operating Temperature, +40 °C Operating Temperature, 65 W, 5 Yr Warranty, 0.8 LB
Weight per unit	0.8000 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

Features

Base	E26
Current Rating	0.111
lumens	850
Power Factor	0.9
Wattage	12

Material, Color, and Finish

color rendering index (cri)	80
color temperature	2700

Descriptions

Description	12W LED BR30 DIM 27K
extra long description	TCP LED12BR30D27K LED 12W BR30 DIM
Special Features	Suitable for Damp Locations

Manufacturer Information

GTIN	00762148243946
sub brand	LED BR Lamps
UPC	762148243946

Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS

Packaging

Carton	12
Package	1
Weight Per each	0.8

Uses, Certifications, and Standards

standard	UL and cUL