SINCE 1945
KEYSTONE
LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED6A19-O-8XX /G2
REPLACEMENT LAMP

DESCRIPTION
5.7W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

- **LAMP TYPE:** A19
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 5.7W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)

TYPICAL APPLICATIONS
- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES
- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Suitable for damp locations
- Operating temperature range –4ºF/–20ºC to 95ºF/35ºC
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Durable Plastic housing lowers the risk for breakage
- Smooth, uniform dimming

ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED6A19-O-827 /G2	A19 bulb. Omni-Directional, dimmable	2700K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-830 /G2	A19 bulb. Omni-Directional, dimmable	3000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-840 /G2	A19 bulb. Omni-Directional, dimmable	4000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-850 /G2	A19 bulb. Omni-Directional, dimmable	5000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W

KEYSTONE SINCE 1945 LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED6A19-O-8XX /G2
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 4.72"
Carton Weight	7.74 lbs

LAMP DIMENSIONS

A (Length)	3.94"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED6A19-O-827 /G2	60 pcs	DOD-54	843654130149
KT-LED6A19-O-830 /G2	60 pcs	KBR-69	843654130156
KT-LED6A19-O-840 /G2	60 pcs	PJC-41	843654137896
KT-LED6A19-O-850 /G2	60 pcs	AKX-31	843654130163

CATALOG NUMBER BREAKDOWN

KT-LED6A19-O-8XX /G2

1 2 3 4 5 6 7 7

1 Keystone Technologies
2 LED Lamp
3 Wattage
4 Lamp Shape
5 Omni-Directional
6 800 Series
7 Color Temperature
8 Generation 2

SINCE 1945
KEYSTONE
LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED6A19-O-8XX /G2
REPLACEMENT LAMP

DESCRIPTION
5.7W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional

- **LAMP TYPE:** A19
- **BASE TYPE:** E26 (Medium)
- **WATTAGE:** 5.7W
- **COLOR TEMPERATURE:** 2700–5000K
- **COLOR RENDERING INDEX (CRI):** >80
- **WARRANTY:** 3 Years
- **RATED LIFE:** L70 (15,000 Hours)

TYPICAL APPLICATIONS
- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES
- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Suitable for damp locations
- Operating temperature range –4ºF/–20ºC to 95ºF/35ºC
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Durable Plastic housing lowers the risk for breakage
- Smooth, uniform dimming

ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED6A19-O-827 /G2	A19 bulb. Omni-Directional, dimmable	2700K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-830 /G2	A19 bulb. Omni-Directional, dimmable	3000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-840 /G2	A19 bulb. Omni-Directional, dimmable	4000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W
KT-LED6A19-O-850 /G2	A19 bulb. Omni-Directional, dimmable	5000K	120V	5.7W	40W	E26	460	>80	230°	Yes	81 lm/W

KEYSTONE SINCE 1945 LIGHT MADE EASY®

ESSENTIAL SERIES
GENERAL PURPOSE LED BULBS

KT-LED6A19-O-8XX /G2
REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 4.72"
Carton Weight	7.74 lbs

LAMP DIMENSIONS

A (Length)	3.94"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED6A19-O-827 /G2	60 pcs	DOD-54	843654130149
KT-LED6A19-O-830 /G2	60 pcs	KBR-69	843654130156
KT-LED6A19-O-840 /G2	60 pcs	PJC-41	843654137896
KT-LED6A19-O-850 /G2	60 pcs	AKX-31	843654130163

CATALOG NUMBER BREAKDOWN

KT-LED6A19-O-8XX /G2

1 2 3 4 5 6 7 7

1 Keystone Technologies
2 LED Lamp
3 Wattage
4 Lamp Shape
5 Omni-Directional
6 800 Series
7 Color Temperature
8 Generation 2