# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## LED82PEV835D 8W Led 2PIN CFL 35K Extended Vertical

*Keystone Technologies*

| | |
|---|---|
| Catalog Number | LED82PEV835D |
| Manufacturer | Keystone Technologies |
| Description | 8W 2-Pin Compact Led Lamp, Extended Vertical Orientation, 120-277V Input, G24D Base, 3500K |
| Weight per unit | 0.2800 (lbs/each) |
| Product Category | Integrated Lamps |

## Features

| | |
|---|---|
| Ballast Type | N/A |
| beam angle | 120 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 900 |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 8 |
| Wire Type | N/A |

## Material, Color, and Finish

| | |
|---|---|
| Base Type | G24d |
| color rendering index (cri) | 80-89 |
| color temperature | 3500 |
| housing color | N/A |

## Descriptions

| | |
|---|---|
| Construction | N/A |
| Description | 8W LED 2PIN CFL 35K EXTENDED VERTICAL |
| extra long description | Key KT-LED82P-EV-835-D-DP 8W , 1000 |
| Long Description | 8W 2-PIN COMPACT LED LAMP, EXTENDED VERTICAL ORIENTATION, 120-277V INPUT, G24D BASE, 3500K |
| Product Type | 8W , 1000 Lumen, Extended Vertical, Bypass 2 Pin & 4 Ballast |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Manufacturer Information

| | |
|---|---|
| Brand | Keystone |
| GTIN | 00890949012819 |
| Manufacturers Part Number | KT-LED82P-EV-835-D-DP |
| UPC | 890949012819 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | LED PLUG-IN (REPLACMENT FOR CFL BIAX LAMPS) |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.28 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Energy Star | N |