


MC GLIDE™



**STOP PULLING AND START GLIDING
TO GET THE JOB DONE FASTER.**

There's a new cable in town. It's called MC Glide™, but you'll call it a miracle.
No more backbreaking pulls. No more damaged studs.
Just a smoother, faster experience.



MC Glide™ features:

Easier pulls. U.S. Patent Pending armor is designed to reduce friction when pulling cable through metal studs and ceilings.

No need for new tools. Works with the same tools and fittings you use with legacy cables.

Time savings. MC Glide™ can be pulled up to 50% faster compared to traditional MC Cable.

Cost reduction. Because MC Glide™ is so much easier, your team can work faster and more efficiently.

Minimize damage to studs. Less resistance means you won't bend or knock down studs.



Take the path of least resistance: visit afcweb.com/mcglide



We completely rethought the profile of MC Glide™.

It's designed to glide through metal studs and ceilings with ease, without sacrificing flexibility or strength, so you can finish the job in half the time.

MC Glide™ Lite® Solid Conductor

Product Code		Trade Size	Grounding Conductor AWG	Approx. Weight/ 1000ft (lb)	Approx. Armor O.D. (in)
250' Coil	1000' Reel				
A004-42-00	A004-60-00	12-2 (Black, White)	12-1 (Green)	103.2	0.460
A004-42-01	A004-60-01	12-2 (Brown, Gray)	12-1 (Green)	103.2	0.460
A004-42-02	A004-60-02	12-2 (Orange, Gray)	12-1 (Green)	103.2	0.460
A004-42-03	A004-60-03	12-2 (Yellow, Gray)	12-1 (Green)	103.2	0.460
A004-42-04	A004-60-04	12-2 (Red, White)	12-1 (Green)	103.2	0.460
A004-42-05	A004-60-05	12-2 (Blue, White)	12-1 (Green)	103.2	0.460
A004-42-07	A004-60-07*	12-2 (Purple, Gray)	12-1 (Green)	103.2	0.460
A005-42-00	A005-60-00	12-3 (Black, Red, White)	12-1 (Green)	129.8	0.495
A005-42-01	A005-60-01	12-3 (Brown, Orange, Gray)	12-1 (Green)	129.8	0.495
A005-42-02	A005-60-02	12-3 (Orange, Yellow, Gray)	12-1 (Green)	129.8	0.495
A005-42-03	A005-60-03	12-3 (Brown, Yellow, Gray)	12-1 (Green)	129.8	0.495
A005-42-04	A005-60-04	12-3 (Red, Blue, White)	12-1 (Green)	129.8	0.495
A005-42-05	A005-60-05	12-3 (Black, Blue, White)	12-1 (Green)	129.8	0.495
A005-42-07	A005-60-07*	12-3 (Brown, Purple, Gray)	12-1 (Green)	129.8	0.495

Note: All dimensions and weights are subject to normal manufacturing tolerances. Other conductor colors available by special order.

* Non-stock items require lead time and minimum quantity order.

Meets UL 1569

U.S. Patent Pending

MC Glide™ Lite® Stranded Conductor

Product Code		Trade Size	Grounding Conductor AWG	Approx. Weight/ 1000ft (lb)	Approx. Armor O.D. (in)
250' Coil	1000' Reel				
A058-42-00	A058-60-00	12-2 (Black, White)	12-1 (Green)	106.4	0.461
A058-42-01	A058-60-01	12-2 (Brown, Gray)	12-1 (Green)	106.4	0.461
A058-42-02	A058-60-02	12-2 (Orange, Gray)	12-1 (Green)	106.4	0.461
A058-42-03	A058-60-03	12-2 (Yellow, Gray)	12-1 (Green)	106.4	0.461
A059-42-00	A059-60-00	12-3 (Black, Red, White)	12-1 (Green)	134.5	0.496
A059-42-01	A059-60-01	12-3 (Brown, Orange, Gray)	12-1 (Green)	134.5	0.496

Note: All dimensions and weights are subject to normal manufacturing tolerances. Other conductor colors available by special order.

Meets UL 1569

U.S. Patent Pending

