ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
802 West Main
Henderson, TX 75652-4459
Phone: 9036571517
Fax: 9036570253



LT3 3" MET L/T, NON UL 25'

SOUTHWIRE COMPANY

Catalog Number	LT3
Manufacturer	SOUTHWIRE COMPANY
Description	Liquidtight Flexible Conduit, 3 in Trade Size, 3.46 to 3.5 in Conduit Outer Diameter, 3.07 to 3.1 in Conduit Inner Diameter, Titan(R) EF Style, 25 ft Length, Galvanized, Gray, 18 in Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 209 lb/100 ft
Weight per unit	1.4 (lbs/each)
Product Category	Liquid Tight Conduit

Features

Outside Diameter	3415

Dimensions and Weight

Diameter	3"
Length	25

Descriptions

Description	3" MET L/T, NON UL 25'
Long Description	Titan2 Type EF is manufactured with a spiral wound interlocked strip of corrosion-resistant galvanized steel. A flame retardant flexible PVC jacket is extruded over the metal core. The gray jacket resists oils mild acids and exposure to sunlight. Black jacket available but subject to economic order quantity. REACH/RoHS-2 (Chemical Limit) Compliant
Product Type	LTM-Ef 3" Gyjt 25CN
Short Description	LTM-EF 3" GyJt 25Cn
Extra Long Description	SWC 55107401 LTM-EF 3" GYJT 25CN

Manufacturer Information

Brand	Southwire
GTIN	00032886043130
UPC	885800

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight

Trade Size

Trade Size	3

Packaging

Carton	25
Weight Per Each	1.4 (lbs/each)