ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



MRC840 ROTATING DIE CRIMP TOOL

BURNDY LLC

Catalog Number	MRC840
Manufacturer	BURNDY LLC
Description	Crimper, #8-4/0 AWG CU.
Weight per unit	8.8 (lbs/each)
Product Category	Crimpers

Features

Tool Type	Mechanical Rotating Crimper
Warranty	5 year limited warranty

Dimensions and Weight

Overall Length	26

Descriptions

Description	ROTATING DIE CRIMP TOOL
Long Description	Crimper, #8-4/0 AWG CU.
Product Type	Rotating Die Crimp Tool
	MRC Series
Special Features	Comfort Grip Handles, Heat Treated Steel Jaws, Approximately 9000 Crimp Cycle Life, Lasts Longer Than Imitations And Will Still Be Working When Others Have Worn Out, 9 Position Color-Coded Rotatable Die Wheel, Engraved Crimp Groove (Die Index Number), Die Index Embossment Allows Permanent Inspectability Of Installed Connectors To Ensure Consistently Reliable And Dependable Connections
Extra Long Description	BUR MRC840 ROTATING DIE CRIMP TOOL

Manufacturer Information

Brand	Burndy-US, a Hubbell affiliate
	BURNDY
GTIN	00781810192504
Manufacturers Part Number	MRC840
UPC	781810

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Crimpers

Packaging

Carton	1
Weight Per Each	8.8 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	CRIMPING
Standard	TAA Compliant (All status valid till December 2024)

Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy
Catalog # MRC840

Crimper, #8-4/0 AWG CU.



Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

Application

Crimping

General

Application - For Use On	Copper Terminals and Splices
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Mechanical Rotating Crimper
Trade Name	HYTOOL™
UPC	781810192504
UPC 12 Digit	7818101925044

Dimensions

Dimensions	26.00 in x 8.00 in x 1.50 in
Height	1.50 in
Length	26.00 in
Weight	8.25 lb
Width	8.00 in

Conductor Related

Crimping Ranges	Copper: #8 AWG- #4/0 AWG

Certifications and Compliance

Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

Catalogs - Full Line BURNDY Catalog
Installation Manuals - BUR_50097800_MRC840
Sales Drawings - SE..211280-01

©2023 Hubbell Incorporated. All rights reserved.