NMLT9050

90 Degree Non-Metallic Connectors

90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.058 lbs/each

Height: 2.242"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 1/2"

Packaging

Unit: 10 pcs

Standard: 50 pcs

Arlington®
1 Stauffer Indsutrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

NMLT9050

90 Degree Non-Metallic Connectors

90 Degree Non-Metallic Connector

Country of Origin: USA

Weight: 0.058 lbs/each

Height: 2.242"

Width: 2.460"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1/2"

Trade Size: 1/2"

Packaging

Unit: 10 pcs

Standard: 50 pcs

Arlington®
1 Stauffer Indsutrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com