ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

PRHELB112X90 1-1/2" 90D Standard Elbow

Robroy/Plasti-Bond

Catalog Number	PRHELB112X90
Manufacturer	Robroy/Plasti-Bond
Description	Elbow, 1-1/2 In Trade Size, 90 ° Connection Orientation, 8.25 In Bend Radius, External Threaded Connection, 12.615 In Length, 448 LB/100
Weight per unit	4.5 (lbs/each)
Product Category	Steel

Features

Bend Angle	90 Degree
End Type	EXTERNAL THREADED
Material	Steel

Descriptions

Additional Information	Color Black; Nipple Length 19-3/4 Inch
Commodity Description	ELBOWS-COUPLINGS-NIPPLES - STEEL
Description	1-1/2" 90D STANDARD ELBOW
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; 2 MIL RED URETHANE (INTERIOR AND THREAD)/40 MIL GRAY PVC (EXTERIOR) FINISH; UL (CANADA AND US), UL 6, CSA C22.2 APPROVAL; ISO 9001 APPLICABLE STANDARD; 10 PER PACK STANDARD PACKAGE; 1-1/2 INCH TRADE SIZE; EXTERNAL THREADED END TYPE; 90 DEGREE BEND ANGLE; 8.25 INCH BEND RADIUS; NIPPLE LENGTH 19-3/4 INCH; THREAD PROTECTOR COLOR BLACK; PRHELB MODEL

Manufacturer Information

Brand	ROBROY
GTIN	00784011200320
Model	Series PRHELB
UPC	784011200320

Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
Type	STANDARD RADIUS

Availability

Manufacturer Status	Non-Stock

Packaging

Carton	1
Package	10
Weight Per each	4.48

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Approval	UL 6/6A, CSA C22.2