



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ADTP703TUV4 Tap Dimmer 700W SP/3W (Tu=Incand) WH

Pass & Seymour/Legrand

Catalog Number	ADTP703TUV4
Manufacturer	Pass & Seymour/Legrand
Description	<P>Turn Lights On or Off, or Even Dim Them, With Just A Soft Tap Of A Finger Thanks to Inventive Micro-Movement Technology. Plus, As A Tru-Universal Dimmer, This Dimmer Switch Self-Calibrates to Work With Virtually Any 120V Dimmable Bulb or Fixture (Excludes 0-10V). Always Adjust to The Precise Light Level You Want, Without The Flicker.</P> <P>This Dimmer* Features Enduring Microban Registered Antimicrobial Technology That Works to Reduce The Growth Of Bacteria, Around The Clock, For The Lifespan Of The PR
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting Dimmers

Features

connection	Screw Terminals
Connection Type	Internal Pressure Plates
Electrical Rating	120V 5A (Fan Control), 120V 16A (Fluorescent), 120V 700W (Halogen), 120V 1600VA (MLV), 120V 700W (Incandescent), 120V 8A (EFL), 120V 450W (LED), 120V 450W (CFL), 120V 700W (ELV)
indoor/outdoor	Indoor
load	Incandescent/Halogen
Load Rating	120V 700W (ELV), 120V 4.5A 450W (CFL), 120V 700W (Halogen), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 4.5A 450W (LED), 120V 700W (Incandescent)
Load Type	Halogen, CFL, LED, Fluorescent, Incandescent
media	Yes
Mounting Type	Wall Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	1
Switch Type	sofTap
Voltage	120.0 V
Voltage Rating	120
Wattage	700
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	White
Finish	Matte



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

Depth	1.62
Width	2.51

Descriptions

Description	TAP DIMMER 700W SP/3W (TU=INCAND) WH
extra long description	P&S ADTP703TUW4 TAP DIMMER 700W SP/
Features	Antimicrobial Protection, Locator Light, Auto-Calibration (Trim), High-End Trim (Dim Range), Low-End Trim (Dim Range)
Long Description	<p>Turn lights on or off, or even dim them, with just a soft tap of a finger thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, this dimmer switch self-calibrates to work with virtually any 120V dimmable bulb or fixture (excludes 0-10V). Always adjust to the precise light level you want, without the flicker.</p> <p>This dimmer* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the pr</p>
Product Type	Tap Dimmer 700W SP/3W (Tu=Incand) W
Special Features	This stylish dimmer switch combines sensitive softTap technology with a gentle dimming paddle to create two unique, sleek lighting control solutions in one. Tru-Universal technology allows for any bulb type and eliminates the flicker.

Manufacturer Information

Brand	legrand
GTIN	00785007023220
Manufacturers Part Number	ADTP703TU-W4
UPC	785007023220

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer

Packaging

Carton	1
Package	4
Weight Per each	0.4

Uses, Certifications, and Standards

Mounting	Box Mount
standard	UL