ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



PVC5X20 SCH 40 5" 20' PVC CONDUIT

HERITAGE PLASTICS

Catalog Number	PVC5X20
Manufacturer	HERITAGE PLASTICS
Description	5 in x 20 ft PVC Schedule 40 Conduit, Belled End
Weight per unit	3.1 (lbs/ft)
Product Category	Conduit & Raceways

Features

Material	PVC
Wall Thickness	0.258
Outside Diameter	5.563

Material, Color, and Finish

Color	Gray

Dimensions and Weight

Height	5.563
Length	240
Width	5.563

Descriptions

Description	SCH 40 5" 20' PVC CONDUIT
Features	Atkore provides the full range of PVC electrical conduit in diameters 1/2" through 8".
Long Description	5 in x 20 ft PVC Schedule 40 Conduit, Belled End
Product Type	PVC SCH40 5 X 20 Ul Be
Short Description	PVC SCH40 5 x 20 UL BE
Extra Long Description	AL-TUBE 8520 PVC SCH40 5 x 20 UL BE

Manufacturer Information

Brand	ATKORE - ALLIED TUBE & CONDUIT
GTIN	00091111085208
Manufacturers Part Number	A52FA42
	8520
UPC	887562

Taxonomies, Classifications, and Categories

Category Description	PVC & ENT
Type	PVC - Sch 40/80

Trade Size

Trade Size	5

Availability

Minimum Qty	20

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	20
Package	760
Weight	3.1048
Weight Per Each	3.1 (lbs/ft)

Uses, Certifications, and Standards

Standard	UL651

PVC Rigid Schedule 40 Conduit

Atkore
Allied Tube & Conduit

- Conforms to UL 651 and NEMA TC 2
- Sunlight resistant per UL 651
- Listed for 90° C conductors or cable
- Product manufactured with one integral solvent-weld bell standard per length



Trade Size	10-foot Length		20-foot Length		Approximate Weight per 100' (lbs)
	Part Number	Crate Quantity (ft)	Part Number	Crate Quantity (ft)	
½	4005010	6,000	4005020	12,000	17
¾	4007510	4,400	4007520	8,800	22
1	4010010	3,600	4010020	7,200	33
1¼	4012510	3,300	4012520	6,600	44
1½	4015010	2,250	4015020	4,500	53
2	4020010	1,400	4020020	2,800	73
2½	4025010	930	4025020	1,860	116
3	4030010	880	4030020	1,760	161
3½	4035010	630	4035020	12,60	194
4	4040010	570	4040020	1,140	229
5	4050010	380	4050020	760	311
6	4060010	260	4060020	520	403
8*	4080010	140	4080020	280	607

Trade Size	Dimensions (in)					
	Average OD	Minimum Average ID	Minimum Wall Thickness, T	Bell Entrance A	Bell Bottom B	Bell Length C
½	0.840	0.578	0.109	0.852	0.836	1.75
¾	1.050	0.780	0.113	1.064	1.046	2.25
1	1.315	1.004	0.133	1.330	1.310	2.25
1¼	1.660	1.335	0.140	1.677	1.655	2.25
1½	1.900	1.564	0.145	1.918	1.894	2.75
2	2.375	2.021	0.154	2.393	2.369	4.00
2½	2.875	2.414	0.203	2.890	2.868	4.00
3	3.500	3.008	0.216	3.515	3.492	4.00
3½	4.000	3.486	0.226	4.015	3.992	4.00
4	4.500	3.961	0.237	4.515	4.491	5.00
5	5.563	4.975	0.258	5.593	5.553	5.75
6	6.625	5.986	0.280	6.658	6.614	6.50
8*	8.625	7.853	0.322	8.670	8.610	6.50

*UL 651 does not include 8"

Intertek