Specifications

Eaton QBGFT1030

Catalog Number: QBGFT1030

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,30A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#10 Cu, #8 Al,QBGF

General specifications

Product Name Eaton QB GFCI circuit breaker	Catalog Number QBGFT1030
UPC 786680130984	Product Length/Depth 1 in
Product Height 1 in	Product Width 1 in
Product Weight 0.5 lb	Warranty 1 year
Certifications UL 489	

Powering Business Worldwide

Physical Attributes

Circuit breaker type
QBGF

Mounting Method
Bolt-on

Number of poles
Single-pole

Type
Ground fault circuit breaker

Wire size
#10 Cu, #8 Al

Performance Ratings

Amperage Rating
30 A

Interrupt rating
10 kAIC

Trip Type
Non-Interchangeable

Trip rating
5 mA trip sensitivity

Voltage rating
120/240 V

Miscellaneous

Special features
5 mA Trip Sensitivity

Resources

Brochures
Loadcenters and Circuit Breakers

Specifications and datasheets
Eaton Specification Sheet - QBGFT1030

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia